

## Electronic housing - DCS 15 M C O S C 7035 - 2203191

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Display housing, 15", light gray, central window, front level, with cutout for connection technology angle plate consisting of two half shells with screws


### Your advantages

- ✓ Display housings for mobile and stationary operator panels
- ✓ Integration of TFT display and membrane keypads
- ✓ Degree of protection: up to IP54
- ✓ Temperature range: -20°C to +50°C
- ✓ Shock-resistant ABS plastic
- ✓ Flammability rating UL 94-V0

RoHS

IP54

### Key Commercial Data

Packing unit	4 pc
GTIN	 4 0 5 5 6 2 6 3 7 8 4 5 9
GTIN	4055626378459

### Technical data

#### Item properties

Type	DCS 15 M C O S C 7035
Order No.	2203191
Housing type	Display housing
Max. IP code to attain	IP54
Battery compartment	no
Wall fastening	no
Ventilation openings present	no

#### Measurements

Width [ w ]	362 mm
Height [ h ]	286 mm

# Electronic housing - DCS 15 M C O S C 7035 - 2203191

## Technical data

### Measurements

Depth [ d ]	62 mm
Diagonal	15 in. (Window for display)
Dimensions	306 mm x 230 mm (Window for display)

### Material specifications

Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0
Housing material	ABS

### Packaging information

Pieces per package	4
Denomination packing units	Pcs.

### Standards and regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

### eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

## Accessories

### Accessories

#### Screwdriver tools

Philips screwdriver - SF-PH 0-60 - 1212558



Screwdriver, PH crosshead, size: PH 0 x 60, 2-component grip, with non-slip grip

### Additional products

## Electronic housing - DCS 15 M C O S C 7035 - 2203191

### Accessories

Seal - DCS 15,0 SEAL - 2203586



Sealing set, including cord and O-rings

---

Display - D T 15,0 XGA L - 2203553



TFT module 15", 1024 x 768 pixels, transmissive/color, LED backlight, white, interface: LVDS, 8 bit, operating temperature: -20 °C ... 70 °C

---

Seal - DCS D-SEAL 3,0MM - 2203749



Sealing strip, self-adhesive, for displays of the DCS housing series (roll: 100 m)

---

Washer/ring - DCS 15,0 WIN 2,5 CLEAR - 2203598



Acrylic glass, satin-finished, frame printed black, for display 800x480

---

Mounting brackets - DCS ADAPT CONNECT - 2203750



Connection technology adapters

## Electronic housing - DCS 15 M C O S C 7035 - 2203191

### Accessories

Mounting set - DCS D-FIX 15,0 - 2203831



Mounting set including plate and screws, for display mounting

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2203191](#)