

Membrane keypad - KP HCS C-MED K16 C3 P8 - 2203568

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Membrane keypad, self-adhesive, silver conduction technology, 16 keys, embossed, 3 colors, connection cable: 62 mm, with crimp female connector RM 2.54 mm, operating temperature -20 °C ... 70 °C

Your advantages

- ✓ Easy integration into electronics housings of the HCS and DCS series
- ✓ Membrane keypads in various sizes and colors for customized device designs
- ✓ Customer-specific key layouts on request

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 474014
GTIN	4055626474014

Technical data

Product properties

Type	KP HCS C-MED K16 C3 P8
Order No.	2203568
Mounting type	adhesive
Number of positions	8
Number of keys	16 (4 x 4)
Number of socket pins	8
Technology	Conductive silver technology
Embossing	Dome embossing 11 x 11 mm

Dimensions

Dimensions	73 mm x 80 mm
Pitch	2.54 mm
Length	62 mm (Membrane cable)

Membrane keypad - KP HCS C-MED K16 C3 P8 - 2203568

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Ambient temperature (operation)	-40 °C ... 80 °C

Packaging details

Pieces per package	1
Denomination packing units	Pcs.

Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Accessories

Additional products

Electronic housing - HCS-C MEDIUM 1W C 1 C 7035 - 2203162



Handheld housing, C-Medium, light gray, consisting of two half shells, front plates above with screws, front 1.1 mm recessed, with window and keypad slot

Electronic housing - HCS-C MEDIUM 1W 3AA 1 1 7035 - 2203163



Handheld housing, C-Medium, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 3 AA batteries

Membrane keypad - KP HCS C-MED K16 C3 P8 - 2203568

Accessories

Electronic housing - HCS-C MAXI 1W C C C 7035 - 2203166



Handheld housing, C-Maxi, light gray, consisting of two half shells with screws, front 1.1 mm recessed with window and keypad slot

Electronic housing - HCS-C MAXI 1W C 1 1 7035 - 2203167



Handheld housing, C-Maxi, light gray, consisting of two half shells, two front plates with screws, front 1.1 mm recessed, with window and keypad slot

Electronic housing - HCS-C MAXI 1W 2X3AA 1 1 7035 - 2203168



Handheld housing, C-Maxi, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 6 AA batteries

Electronic housing - HCS-C MAXI 1W 2X9V 1 1 7035 - 2203170



Handheld housing, C-Maxi, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 2x 9 V battery

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2203568](#)