

Membrane keypad - KP HC-ALU 100 K4 C4 P6 - 2203574

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Membrane keypad, self-adhesive, copper conduction technology, 4 keys, embossed, 4 colors, connection cable: 47.3 mm, RM 1.0 mm, operating temperature -20°C ... 70°C



RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 485270
GTIN	4055626485270

Technical data

Product properties

Type	KP HC-ALU 100 K4 C4 P6
Order No.	2203574
Mounting type	adhesive
Number of positions	4
Number of keys	4
Number of socket pins	6
Technology	Conductive silver technology
Embossing	Dome embossing 11 x 11 mm

Dimensions

Dimensions	95 mm x 72 mm
Pitch	1 mm
Length	47.3 mm (Membrane cable)

Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Ambient temperature (operation)	-40 °C ... 80 °C

Packaging details

Membrane keypad - KP HC-ALU 100 K4 C4 P6 - 2203574

Technical data

Packaging details

Pieces per package	1
Denomination packing units	Pcs.

Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2203574](#)