

Interface module - VIP-3/SC/HD62SUB/M - 2322391

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with screw connection and high density D-SUB miniature pin strip, for mounting on NS 35 rails, no. of pos.: 62, width: 180 mm

Your advantages

- ☒ Screw connection
- ☒ 1:1 connection



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356451697

Technical data

Dimensions

Width	113.5 mm
Height	69 mm
Depth	62 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	25 V AC
	60 V DC
Max. perm. current (per branch)	1 A
Number of positions	62
Status display	No
Mounting position	any

Interface module - VIP-3/SC/HD62SUB/M - 2322391

Technical data

Connection data

Connection name	Field level
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	62
Conductor cross section solid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Connection data 2

Connection name	Controller level
Connection method	High density D-SUB pin strip
Number of connections	1
Number of positions	62

Standards and Regulations

Connection in acc. with standard	CUL
Standards/regulations	EN 50178
Flammability rating according to UL 94	V0


Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings


Interface module - VIP-3/SC/HD62SUB/M - 2322391

Dimensional drawing



Interface module - VIP-3/SC/HD62SUB/M - 2322391

Circuit diagram



Universal circuit diagram

Classifications

eCl@ss

eCl@ss 10.0.1	27141152
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27250300
eCl@ss 5.1	27250300
eCl@ss 6.0	27242600
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

ETIM

ETIM 4.0	EC002780
ETIM 5.0	EC002780
ETIM 6.0	EC002780
ETIM 7.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421

Interface module - VIP-3/SC/HD62SUB/M - 2322391

Classifications

UNSPSC

UNSPSC 12.01	39121421
UNSPSC 13.2	39121432
UNSPSC 18.0	39121432
UNSPSC 19.0	39121432
UNSPSC 20.0	39121432
UNSPSC 21.0	39121432

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN	125 V		
Nominal current IN	1 A		
mm²/AWG/kcmil	30-12		

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN	125 V		
Nominal current IN	1 A		
mm²/AWG/kcmil	30-12		

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------

Interface module - VIP-3/SC/HD62SUB/M - 2322391

Approvals

cULus Recognized



Accessories

Accessories

System cable

Cable - CABLE-D62SUBH/B/B/ 40/K4G/GK2 - 2319090



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 0.4 m

Cable - CABLE-D62SUBH/B/B/ 60/K4G/GK2 - 2319087



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 0.6 m

Cable - CABLE-D62SUBH/B/B/ 200/K4G/GK2 - 2312000



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 2 m

Cable - CABLE-D62SUBH/B/B/ 300/K4G/GK2 - 2311991



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 3 m

Interface module - VIP-3/SC/HD62SUB/M - 2322391

Accessories

Cable - CABLE-D62SUBH/B/B/ 400/K4G/GK2 - 2311988



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 4 m

Cable - CABLE-D62SUBH/B/B/ 500/K4G/GK2 - 2311975



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 5 m

Cable - CABLE-D62SUBH/B/B/ 750/K4G/GK2 - 2311962



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 7.5 m

Cable - CABLE-D62SUBH/B/B/1000/K4G/GK2 - 2311959



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 10 m

Cable - CABLE-D62SUBH/B/B/1250/K4G/GK2 - 2311946



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 12.5 m

Interface module - VIP-3/SC/HD62SUB/M - 2322391

Accessories

Cable - CABLE-D62SUBH/B/B/1500/K4G/GK2 - 2311933



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 15 m

Cable - CABLE-D62SUBH/B/B/1750/K4G/GK2 - 2311920



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 17.5 m

Cable - CABLE-D62SUBH/B/B/2000/K4G/GK2 - 2311917



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 20 m

Cable - CABLE-D62SUBH/B/B/3000/K4G/GK2 - 2901375



Assembled, shielded round cable, with 62-pos. HD D-SUB female connector at both ends; cable length: 30 m

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2322391](#)