

Monitor - BL FPM 21.5 - 2400515

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



IP65-rated, 21.5-inch, flat panel LCD monitor with projected capacitive touch screen

Product Description

The Baseline BL FPM 21.5 is an industrial flat-panel monitor that can be used in applications where a remote display location is required.

Your advantages

- ✓ 21.5-inch display
- ✓ DisplayPort 1.2, VGA, and DVI-I input ports
- ✓ Integrated configuration buttons
- ✓ Ambient operating temperatures from -10°C to 60°C
- ✓ 21.5-inch touch screen display

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 076201
GTIN	4055626076201

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Display

Display type	54.6 cm / 21.5"-TFT
Screen resolution	1920 x 1080 Pixel(s) (Full HD)
Touch technology	projective-capacitive, ten-touch control
Brightness	300 cd/m², typical (adjustable)
Backlighting	LED
Display backlight MTBF	> 50000 h

Monitor - BL FPM 21.5 - 2400515

Technical data

Display

Colors	16.7 million colors
--------	---------------------

Monitor data

Network	Without network
Interfaces	1x USB Type A (For touch control only)
Monitor output	1x DisplayPort
	1x DVI-D
	1x VGA
Slots	without slots
Optical drive	without drive

General

Mounting type	VESA MIS-D, 100
	Front installation
Weight	7.87 kg

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	10 % ... 90 % (non-condensing)
Vibration (operation)	1g
Shock	15g, 11 ms impulse

Device supply

Supply voltage	24 V DC (±10 %)
Power supply unit	24 V DC

Standards and Regulations

Shock	15g, 11 ms impulse
Vibration (operation)	1g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19200103
eCl@ss 4.0	24010600
eCl@ss 4.1	24010600

Monitor - BL FPM 21.5 - 2400515

Classifications

eCl@ss

eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242301
eCl@ss 8.0	19200201
eCl@ss 9.0	19200103

ETIM

ETIM 3.0	EC001425
ETIM 4.0	EC001428
ETIM 5.0	EC001428
ETIM 6.0	EC001414
ETIM 7.0	EC001414

UNSPSC

UNSPSC 6.01	43172401
UNSPSC 7.0901	43211902
UNSPSC 11	43172401
UNSPSC 12.01	43211902
UNSPSC 13.2	43211902
UNSPSC 18.0	43211509
UNSPSC 19.0	43211509
UNSPSC 20.0	43211509
UNSPSC 21.0	43211509

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 238705

Monitor - BL FPM 21.5 - 2400515

Approvals

cUL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 238705

cULus Listed



Accessories

Accessories

Mounting material

Mounting flange - BL FPM MOUNTING KIT - 2403287



IPC mounting block style C. Compatible with BL FPM...

Connecting cable - VL 2.0M DP CABLE - 2404774



DisplayPort (DP) cable (2 m) for use with industrial computers

Spare parts

Printed-circuit board connector - MSTB 2,5/ 3-STF - 1786844



PCB connector, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 3, pitch: 5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2400515](#)