

Slave protocol chip - IBS SUPI 3 OPC T&R - 2746964

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Slave protocol chip, for INTERBUS

RoHS

Key Commercial Data

Packing unit	1000 pc
Minimum order quantity	1000 pc
GTIN	 4 017918 932190
GTIN	4017918932190

Technical data

Dimensions

Width	14 mm
Height	1.2 mm
Depth	14 mm
Length	14 mm

Module

IC power supply voltage	5 V DC $\pm 10\%$ (DC)
Internal data length	4 bytes internally, external expansion is possible up to 64 bytes
User interface	MFP interface, digital I/O (2-8 IN/OUT, 16 IN/16OUT), SPI master interface (direct serial coupling to ADC/DACs) and serial microprocessor interface

General

Type	TQFP 64 (with copper block)
------	-----------------------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Slave protocol chip - IBS SUPI 3 OPC T&R - 2746964

Classifications

eCl@ss

eCl@ss 10.0.1	27242605
eCl@ss 4.0	27250200
eCl@ss 4.1	27250200
eCl@ss 5.0	27249200
eCl@ss 5.1	27249200
eCl@ss 6.0	27242600
eCl@ss 7.0	27242608
eCl@ss 8.0	27242608
eCl@ss 9.0	27242605

ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001601
ETIM 4.0	EC001604
ETIM 5.0	EC001604
ETIM 6.0	EC001601
ETIM 7.0	EC001601

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	32151602
UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602
UNSPSC 21.0	32151602

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2746964