

Slave protocol chip - IBS SUPI 3 LS - 2746977

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Slave protocol chip, for INTERBUS



RoHS

Key Commercial Data

Packing unit	160 pc
Minimum order quantity	160 pc
GTIN	 4 017918 472788
GTIN	4017918472788

Technical data

Dimensions

Width	12 mm
Depth	12 mm
Length	12 mm

Ambient conditions

Ambient temperature (storage/transport)	5 °C ... 30 °C (at max. 60 %)
Ambient temperature (operation)	-40 °C ... 85 °C (at max. 75% humidity during operation)

Module

IC power supply voltage	5 V DC $\pm$ 10 % (DC)
Typical current consumption	40 mA
Connection method	Remote bus/local bus
Interface	INTERBUS
Internal data length	32-bit internal, external expansion possible

General

Type	TQFP 44
------	---------

Environmental Product Compliance

Slave protocol chip - IBS SUPI 3 LS - 2746977

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27242605
eCl@ss 4.0	27250200
eCl@ss 4.1	27250200
eCl@ss 5.0	27249200
eCl@ss 5.1	27249200
eCl@ss 6.0	27242600
eCl@ss 7.0	27242608
eCl@ss 8.0	27242608
eCl@ss 9.0	27242605

ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001601
ETIM 4.0	EC001604
ETIM 5.0	EC001604
ETIM 6.0	EC001601
ETIM 7.0	EC001601

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	32151602
UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602
UNSPSC 21.0	32151602

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2746977](#)