

Interface converter - PSM-EG-RS232/RS485-P/2D - 2761392

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Interface converter, for converting RS-232 to RS-485 2-wire, with electrical isolation, DIN-rail mountable

The figure shows a variant of the V.24 (RS-232)/RS-422 converter



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 064686
GTIN	4017918064686

Technical data

Dimensions

Width	45 mm
Height	75 mm
Depth	110 mm

Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
---------------------------------	----------------

General

Bit delay	≤ 3 µs
Bit distortion	≤ 5 %
Electrical isolation	VCC // V.24 (RS-232) // RS-485
Test voltage data interfaces	2.5 kV AC
Test voltage data interface/power supply	2.5 kV AC
	2.5 kV
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Net weight	293.6 g
Housing material	ABS

Interface converter - PSM-EG-RS232/RS485-P/2D - 2761392

Technical data

General

Color	green
-------	-------

Power supply

Nominal supply voltage	24 V DC $\pm 20\%$
Typical current consumption	130 mA (24 V DC)

Interfaces

Transmission length	15 m (twisted pair)
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	14

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Connection in acc. with standard	CUL

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19179290
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27242200
eCl@ss 5.1	27242200
eCl@ss 6.0	19179200
eCl@ss 7.0	19179290
eCl@ss 8.0	19179290
eCl@ss 9.0	19179290

ETIM

ETIM 2.0	EC000698
ETIM 3.0	EC000698
ETIM 4.0	EC001467
ETIM 5.0	EC000310
ETIM 6.0	EC000310
ETIM 7.0	EC000310

Interface converter - PSM-EG-RS232/RS485-P/2D - 2761392

Classifications

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	43222604
UNSPSC 18.0	43222604
UNSPSC 19.0	43222604
UNSPSC 20.0	43222604
UNSPSC 21.0	43222604

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized



Accessories

Accessories

Adapter cable

Data cable - PSM-KA9SUB9/BB/2METER - 2799474



RS-232 cable, 9-pos. D-SUB socket on 9-pos. D-SUB socket, 9-wire, 1:1

Data plug

Interface converter - PSM-EG-RS232/RS485-P/2D - 2761392

Accessories

D-SUB bus connector - SUBCON 9/M-SH - 2761509



D-SUB connector, 9-pos., male connector, one cable entry < 35°, universal type for all systems, pin assignment: 1, 2, 3, 4, 5, 6, 7, 8, 9 to screw connection terminal block

Interface converter

Interface converter - PSM-ME-RS232/RS485-P - 2744416



Interface converter, for converting RS-232 (V.24) to RS-422 (V.11) and RS-485, with electrical isolation, 2 channels, rail-mountable

Mounting material

Shield connection clamp - ME-SAS - 2853899



Shield connection clamp for printed circuit terminal block

Screwdriver tools

Screwdriver - SZF 1-0,6X3,5 - 1204517



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2761392