

## Cable - CAB-TE MR36F/OE/24/S/30M - 2909736

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid  
(<http://phoenixcontact.com/download>)



Migration cable for Bailey INFI 90 to modern control platforms. Open-end cable for universal configurations, 36 conductors, 30.0 m

### Your advantages

- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Open end at one end
- MR connector at one end
- 1:1 connection

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 055626 682617
GTIN	4055626682617

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Max. permissible operating voltage	125 V AC
	125 V DC
Max. current carrying capacity per path	1 A
Length of cable	30 m
External cable diameter	10.5 mm
Single wire, cross section	0.25 mm <sup>2</sup>
Single wire, cross section [AWG]	24
Shielding	yes
	Overall foil and braid shield

#### Supported controller

# Cable - CAB-TE MR36F/OE/24/S/30M - 2909736

## Technical data

### Supported controller

Controller	Bailey INFI 90
------------	----------------

### Color code

Connector 1 = connector 2 (optional) = wire color	MR36F (1) = black
	MR36F (2) = white
	MR36F (3) = red
	MR36F (4) = green
	MR36F (5) = orange
	MR36F (6) = blue
	MR36F (7) = white-black
	MR36F (8) = red-black
	MR36F (9) = green-black
	MR36F (10) = orange-black
	MR36F (11) = blue-black
	MR36F (12) = black-white
	MR36F (13) = red-white
	MR36F (14) = green-white
	MR36F (15) = blue-white
	MR36F (16) = black-red
	MR36F (17) = white-red
	MR36F (18) = orange-red
	MR36F (19) = blue-red
	MR36F (20) = red-green
	MR36F (21) = orange-green
	MR36F (22) = black-white-red
	MR36F (23) = white-black-red
	MR36F (24) = red-black-white
	MR36F (25) = green-black-white
	MR36F (26) = orange-black-white
	MR36F (27) = blue-black-white
	MR36F (28) = black-red-green
	MR36F (29) = white-red-green
	MR36F (30) = red-black-green
	MR36F (31) = green-black-orange
	MR36F (32) = orange-black-green
	MR36F (33) = blue-white-orange
	MR36F (34) = black-white-orange
	MR36F (35) = white-red-orange
	MR36F (36) = orange-white-blue

## Cable - CAB-TE MR36F/OE/24/S/30M - 2909736

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27242220
eCl@ss 5.0	27242200
eCl@ss 5.1	27242200
eCl@ss 6.0	27249200
eCl@ss 7.0	27249205
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

#### ETIM

ETIM 5.0	EC000237
ETIM 6.0	EC000237
ETIM 7.0	EC000237

### Approvals

#### Approvals

---

#### Approvals

---

#### EAC

---

#### Ex Approvals

---

#### Approval details

EAC		RU*- DE.HB*35.B00385
-----	-------------------------------------------------------------------------------------	-------------------------

### Accessories

#### Accessories

#### Marker carrier cable

#### Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2909736](#)