

## Covering hood - AH-ME - 3240265

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cover, for the contact- and dust-protected encapsulation of the components

### Your advantages

- ✓ The cover can be securely snapped onto the corresponding APH-ME end brackets and sealed as an option
- ✓ Cover profiles provide protection against unauthorized actuation of terminal strips
- ✓ The AH-ME cover, which is enclosed on all sides, is snapped onto the end brackets and can be sealed as an option
- ✓ This profile has been specially adapted to the shape of the test disconnect terminal blocks

RoHS

### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 046356 462884
GTIN	4046356462884

### Technical data

#### General

Color	transparent
Material	PC
Flammability rating according to UL 94	V2

#### Dimensions

Width	150 mm
Length	200 mm
Height	78 mm

#### General

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C)

## Covering hood - AH-ME - 3240265

### Technical data

#### General

Permissible humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

#### Standards and Regulations


Flammability rating according to UL 94	V2
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Drawings

Dimensional drawing



## Covering hood - AH-ME - 3240265

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27141190
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141190
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

#### ETIM

ETIM 5.0	EC002848
ETIM 6.0	EC002848
ETIM 7.0	EC002848

#### UNSPSC

UNSPSC 13.2	39121421
UNSPSC 18.0	39121410
UNSPSC 19.0	39121410
UNSPSC 20.0	39121410
UNSPSC 21.0	39121410

### Approvals

#### Approvals

Approvals

EAC

Ex Approvals

#### Approval details

EAC		EAC-Zulassung
-----	---	---------------

### Accessories

Accessories

Cover profile carrier

## Covering hood - AH-ME - 3240265

### Accessories

Cover profile carrier - E/NS 35 N-APH - 3240269



Cover profile carrier, width: 9.5 mm, height: 77.5 mm, material: PA, length: 48.6 mm, for covering hoods, color: gray

---

Cover profile carrier - APH-ME - 3034374



Cover profile carrier, for mounting on NS 35/7,5 DIN rail, for fixing the AP-ME cover profile, can be sealed as an option

---

Cover profile carrier - APT-ME - 3034358



Cover profile carrier for mounting on NS 35/7.5 DIN rail for attaching the cover profile AP-ME

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3240265