

Cable tie - WT-HF 4,5X200 BK-L - 3240762

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable binders for quick and secure bundling, standard version

RoHS

Key Commercial Data

Packing unit	1000 pc
Minimum order quantity	1000 pc
GTIN	 4 046356 704809
GTIN	4046356704809

Technical data

Dimensions

Length (b)	200 mm
Width (a)	4.8 mm
Cable diameter	3 mm ... 50 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Optimum ambient temperature (storage/transport)	23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.
Short-term temperature	110 °C

General

Color	black
-------	-------

Cable tie - WT-HF 4,5X200 BK-L - 3240762

Technical data

General

Type	Internal teeth
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA 6.6
Tensile strength	220 N

Standards and Regulations

Resistance to UV radiation	no
Connection in acc. with standard	UL
Flammability rating according to UL 94	V2

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27140702
eCl@ss 4.0	27140700
eCl@ss 4.1	27140700
eCl@ss 5.0	27140700
eCl@ss 5.1	27140700
eCl@ss 6.0	27140700
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702
eCl@ss 9.0	27140702

ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046
ETIM 6.0	EC000046
ETIM 7.0	EC000046

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703
UNSPSC 18.0	39121731

Cable tie - WT-HF 4,5X200 BK-L - 3240762

Classifications

UNSPSC

UNSPSC 19.0	39121731
UNSPSC 20.0	39121731
UNSPSC 21.0	39121731

Approvals

Approvals

Approvals

DNV / BV / GL / LR / RINA / UL Recognized

Ex Approvals

Approval details

DNV



<http://exchange.dnv.com/tari/>

BV



<http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials>

GL



<https://approvalfinder.dnvgl.com/>

LR



<http://www.lr.org/en>

RINA



<http://www.rina.org/en>

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

Cable tie - WT-HF 4,5X200 BK-L - 3240762

Accessories

Accessories

Universal tools

Cable tie tool - UNIFOX-CT 4,8 - 1212475



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Cable tie tool - UNIFOX-CT 4,8P - 1212609



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3240762