

Protective hose - WP-SPIRAL PU C HF 14 - 3240857

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective hose, spring steel wire with PU coating, highly stranded

RoHS

Key Commercial Data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 736831
GTIN	4046356736831

Technical data

Dimensions

Inner diameter (f)	10 mm
Outside diameter	14 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Short-term temperature	120 °C
Degree of protection	IP68

General

Color	blue
Type	Spring steel wire with PU coating
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V2
Material	PU
Bending radius, static	10 mm
Bending radius, dynamic	25 mm
Tensile strength	100 N

Protective hose - WP-SPIRAL PU C HF 14 - 3240857

Technical data

Standards and Regulations

Resistance to UV radiation	no
Halogen-free	yes
Flammability rating according to UL 94	V2

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27430304
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27430304
eCl@ss 8.0	27430304
eCl@ss 9.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177
ETIM 6.0	EC001177
ETIM 7.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

Approvals

Approvals

Protective hose - WP-SPIRAL PU C HF 14 - 3240857

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G PP HF PG9 - 3240989



Cable gland made from PP with Pg thread, IP65 protection

Screw connection - WP-G PP HF M12 - 3240996



Cable gland made from PP with metric thread, IP65 protection

Screw connection - WP-GT PP HF PG9 - 3241003



Cable gland made from PP with Pg thread, rotatable, IP54 protection

Protective hose - WP-SPIRAL PU C HF 14 - 3240857

Accessories

Screw connection - WP-GT PP HF M16 - 3241011



Cable gland made from PP with metric thread, rotatable, IP54 protection

Mounting material

Hose clamp - WP-BASE HF 14 - 3240967



Hose clamps

Protective cap

Cable protection end sleeve - WP-SC HF 14 - 3241017



End sleeves as cable protection

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3240857