

## Screw connection - WP-GA HF IP66 PG9 BK - 3240917

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Pg thread, IP66 protection, angled

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 50 pc                                                                                                   |
| Minimum order quantity | 50 pc                                                                                                   |
| GTIN                   | <br>4 046356 710244 |
| GTIN                   | 4046356710244                                                                                           |

### Technical data

#### Dimensions

|                  |                 |
|------------------|-----------------|
| Length (b)       | 34 mm           |
| Width (a)        | 20 mm           |
| Height (c)       | 37 mm           |
| Diameter         | 20 mm           |
| Outside diameter | 13 mm           |
| Cable diameter   | 13 mm ... 13 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 115 °C |
| Degree of protection            | IP66              |

#### General

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Color                                  | black                                    |
| Type                                   | Angled                                   |
|                                        | Outer thread                             |
| Components                             | free from silicone, halogen, and cadmium |
| Flammability rating according to UL 94 | V2                                       |
| Material                               | PA                                       |

## Screw connection - WP-GA HF IP66 PG9 BK - 3240917

### Technical data

#### Standards and Regulations

|                                        |     |
|----------------------------------------|-----|
| Halogen-free                           | yes |
| Connection in acc. with standard       | UL  |
| Flammability rating according to UL 94 | V2  |

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27144432 |
| eCl@ss 4.0    | 27141200 |
| eCl@ss 4.1    | 27141200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27149109 |
| eCl@ss 8.0    | 27149109 |
| eCl@ss 9.0    | 27144432 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC001178 |
| ETIM 5.0 | EC001178 |
| ETIM 6.0 | EC000441 |
| ETIM 7.0 | EC000441 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121311 |
| UNSPSC 18.0   | 39121311 |
| UNSPSC 19.0   | 39121311 |
| UNSPSC 20.0   | 39121311 |
| UNSPSC 21.0   | 39121311 |

### Approvals

#### Approvals

## Screw connection - WP-GA HF IP66 PG9 BK - 3240917

### Approvals

#### Approvals

LR / UL Recognized / VDE Zeichengenehmigung

#### Ex Approvals

#### Approval details

|                        |                                                                                     |                                                                                                                                                                                                           |
|------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| LR                     |    | <a href="http://www.lr.org/en">http://www.lr.org/en</a>                                                                                                                                                   |
| UL Recognized          |    | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>                                                     |
| VDE Zeichengenehmigung |  | <a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a> |

### Accessories

#### Accessories

##### Corrugated pipe

Protective hose - WP-PA HF 13,0 BK - 3240681



Polyamide protective hose, inflammability class V0, UV resistant

Protective hose - WP-PA HF-HB 13,0 BK - 3240839



Polyamide protective hose, inflammability class HB, UV resistant

#### Seal

## Screw connection - WP-GA HF IP66 PG9 BK - 3240917

### Accessories

Gasket - WP-OR PG9 - 3241195

Gasket, height: 1.5 mm, diameter: 16 mm, color: black



---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240917](#)