

Screw connection - WP-GA HF IP66 PG29 BK - 3240921

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Pg thread, IP66 protection, angled

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 710282
GTIN	4046356710282

Technical data

Dimensions

Length (b)	65 mm
Width (a)	44 mm
Height (c)	67.5 mm
Diameter	43 mm
Outside diameter	34.5 mm
Cable diameter	34.5 mm ... 34.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP66

General

Color	black
Type	Angled
	Outer thread
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V2
Material	PA

Screw connection - WP-GA HF IP66 PG29 BK - 3240921

Technical data

Standards and Regulations

Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	V2

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27144432
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178
ETIM 6.0	EC000441
ETIM 7.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121311
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

Approvals

Approvals

Screw connection - WP-GA HF IP66 PG29 BK - 3240921

Approvals

Approvals

LR / UL Recognized / VDE Zeichengenehmigung

Ex Approvals

Approval details

LR



<http://www.lr.org/en>

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 34,5 BK - 3241088



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 25 m

Protective hose - WP-PA HF-HB 34,5 BK - 3240843



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 25 m

Mounting material

Screw connection - WP-GA HF IP66 PG29 BK - 3240921

Accessories

Protective hose fixing bracket - WP-BASE A PG29 - 3241081



Fixing bracket for protective sleeves, fixed with two screws

Seal

Gasket - WP-OR PG29 - 3241199



Gasket, height: 2 mm, diameter: 38 mm, color: black

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3240921