

## Screw connection - WP-G PP HF PG21 - 3240992

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from PP with Pg thread, IP65 protection

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 046356 711241 |
| GTIN                   | 4046356711241                                                                                           |

### Technical data

#### Dimensions

|                  |                     |
|------------------|---------------------|
| Width (a)        | 44 mm               |
| Height (c)       | 48 mm               |
| Wrench size      | 36 mm               |
| Outside diameter | 27 mm               |
| Cable diameter   | 19.5 mm ... 19.5 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -10 °C ... 110 °C |
| Degree of protection            | IP65              |

#### General

|                                        |              |
|----------------------------------------|--------------|
| Color                                  | gray         |
| Type                                   | Straight     |
|                                        | Outer thread |
| Components                             | halogen-free |
| Flammability rating according to UL 94 | HB           |
| Material                               | PP           |

## Screw connection - WP-G PP HF PG21 - 3240992

### Technical data

#### Standards and Regulations

|                                        |     |
|----------------------------------------|-----|
| Halogen-free                           | yes |
| Flammability rating according to UL 94 | HB  |

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27144432 |
| eCl@ss 4.0    | 27141200 |
| eCl@ss 4.1    | 27141200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27149109 |
| eCl@ss 8.0    | 27149109 |
| eCl@ss 9.0    | 27144432 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC001178 |
| ETIM 5.0 | EC001178 |
| ETIM 6.0 | EC000441 |
| ETIM 7.0 | EC000441 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121311 |
| UNSPSC 18.0   | 39121311 |
| UNSPSC 19.0   | 39121311 |
| UNSPSC 20.0   | 39121311 |
| UNSPSC 21.0   | 39121311 |

### Approvals

#### Approvals

## Screw connection - WP-G PP HF PG21 - 3240992

### Approvals

Approvals

VDE Zeichengenehmigung

---

Ex Approvals

---

### Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

### Accessories

Accessories

Corrugated pipe

Protective hose - WP-SPIRAL PVC C 27 - 3240853



Protective hose, spring steel wire with PVC coating, highly stranded

---

Protective hose - WP-SPIRAL PU C HF 27 - 3240860




Protective hose, spring steel wire with PU coating, highly stranded

---

### Mounting material

Protective hose fixing bracket - WP-BASE A PG21 - 3241080



Fixing bracket for protective sleeves, fixed with two screws

---

Seal

## Screw connection - WP-G PP HF PG21 - 3240992

### Accessories

Gasket - WP-OR PG21 - 3241198

Gasket, height: 2 mm, diameter: 30 mm, color: black



---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3240992