

Screw connection - WP-GT PP HF PG16 - 3241005

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from PP with Pg thread, rotatable, IP54 protection

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 711371
GTIN	4046356711371

Technical data

Dimensions

Width (a)	30 mm
Height (c)	48 mm
Wrench size	27 mm
Outside diameter	21 mm
Cable diameter	14.5 mm ... 14.5 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
Degree of protection	IP54

General

Color	gray
Type	Rotatable
	Outer thread
Components	halogen-free
Flammability rating according to UL 94	HB
Material	PP

Screw connection - WP-GT PP HF PG16 - 3241005

Technical data

Standards and Regulations

Halogen-free	yes
Flammability rating according to UL 94	HB

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27144432
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178
ETIM 6.0	EC000441
ETIM 7.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121311
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

Approvals

Approvals

Screw connection - WP-GT PP HF PG16 - 3241005

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

Accessories

Accessories

Corrugated pipe

Protective hose - WP-SPIRAL PVC C 21 - 3240852



Protective hose, spring steel wire with PVC coating, highly stranded

Protective hose - WP-SPIRAL PU C HF 21 - 3240859



Protective hose, spring steel wire with PU coating, highly stranded

Mounting material

Protective hose fixing bracket - WP-BASE A PG16 - 3241079



Fixing bracket for protective sleeves, fixed with two screws

Seal

Screw connection - WP-GT PP HF PG16 - 3241005

Accessories

Gasket - WP-OR PG16 - 3241197

Gasket, height: 2 mm, diameter: 24 mm, color: black



Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3241005](#)