

Spiral tube - WG-S HF 50 - 3241115

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Spiral hose, for easy bundling and guiding of cables and conductors, offers protection against slight mechanical strain

RoHS

Key Commercial Data

Packing unit	25 M
Minimum order quantity	25 M
GTIN	 4 046356 717441
GTIN	4046356717441

Technical data

Dimensions

Length (b)	25 m
Width (a)	50 mm
Inner diameter (f)	8.2 mm
Cable diameter	12 mm ... 50 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 85 °C
Ambient temperature (assembly)	-20 °C ... 60 °C

General

Color	transparent
Type	Continuous strip
Components	free from silicone and halogen
Flammability rating according to UL 94	HB
Material	PE

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Spiral tube - WG-S HF 50 - 3241115

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27430302
eCl@ss 4.0	27140600
eCl@ss 4.1	27140600
eCl@ss 5.0	27140600
eCl@ss 5.1	27140600
eCl@ss 6.0	27400700
eCl@ss 7.0	27430302
eCl@ss 8.0	27430302
eCl@ss 9.0	27430302

ETIM

ETIM 3.0	EC000012
ETIM 4.0	EC000046
ETIM 5.0	EC002604
ETIM 6.0	EC002604
ETIM 7.0	EC002604

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121708
UNSPSC 13.2	39131712
UNSPSC 18.0	39131712
UNSPSC 19.0	39131712
UNSPSC 20.0	39131712
UNSPSC 21.0	39131712

Accessories

Accessories

Cutting tools

Spiral tube - WG-S HF 50 - 3241115

Accessories

Cable-cutting tool - CUTFOX-ES - 1212621



Electrician's scissors, high cutting performance thanks to micro-serrated cutting area, suitable for copper, aluminum, Kevlar fibers, and plastic, two-component non-slip soft-grip handles, ergonomic design, adjustable screw joint

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3241115](#)