

## Nut - WP-CN BRASS M10 - 3241145

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Nut, height: 2.8 mm, color: silver



### Your advantages

- ✓ The brass counter nuts are used to lock protective hose screw connections in the case of bore holes without a thread.
- ✓ Metric thread according to EN 50262

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 100 pc                                                                                                  |
| GTIN         | <br>4 046356 785518 |
| GTIN         | 4046356785518                                                                                           |

### Technical data

#### Dimensions

|             |          |
|-------------|----------|
| Height (c)  | 2.8 mm   |
| Wrench size | 14.00 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 200 °C |
|---------------------------------|-------------------|

#### General

|            |                                |
|------------|--------------------------------|
| Color      | silver                         |
| Components | free from silicone and halogen |
| Material   | Brass, nickel-plated           |

### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

## Nut - WP-CN BRASS M10 - 3241145

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27144424 |
| eCl@ss 4.0    | 23110700 |
| eCl@ss 4.1    | 23110700 |
| eCl@ss 5.0    | 23110700 |
| eCl@ss 5.1    | 23110700 |
| eCl@ss 6.0    | 23110700 |
| eCl@ss 7.0    | 23110701 |
| eCl@ss 8.0    | 23110701 |
| eCl@ss 9.0    | 27144424 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000519 |
| ETIM 4.0 | EC000519 |
| ETIM 5.0 | EC000129 |
| ETIM 6.0 | EC000940 |
| ETIM 7.0 | EC000940 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 31161727 |
| UNSPSC 18.0   | 31161716 |
| UNSPSC 19.0   | 31161716 |
| UNSPSC 20.0   | 31161716 |
| UNSPSC 21.0   | 31161716 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3241145](#)