

Flat gasket - WP-FS IP68 M10 - 3241159

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Flat gasket, height: 1.6 mm, diameter: 17 mm, color: black



Your advantages

- ✓ The Perbunan flat sealing rings are used to seal protective hose screw connections on uneven surfaces.
- ✓ Up to IP68 protection is achieved.

RoHS

Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 785655
GTIN	4046356785655

Technical data

Dimensions

Height (c)	1.6 mm
Diameter	17 mm
Inner diameter (f)	10 mm
Material thickness (g)	1.6 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 120 °C
Degree of protection	IP68

General

Color	black
Components	free from silicone and halogen
Material	Perbunan

Environmental Product Compliance

Flat gasket - WP-FS IP68 M10 - 3241159

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27430319
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	21132000
eCl@ss 5.1	21132000
eCl@ss 6.0	21132000
eCl@ss 7.0	27439218
eCl@ss 8.0	27439218
eCl@ss 9.0	27430319

ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001181
ETIM 6.0	EC001181
ETIM 7.0	EC001181

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39131608
UNSPSC 18.0	39131608
UNSPSC 19.0	39131608
UNSPSC 20.0	39131608
UNSPSC 21.0	39131608

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3241159](#)