

Corrugated tube screw connection - WP-GR HF CTA M40 BK - 3241223

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Corrugated pipe adapter, with M40 internal thread, straight, black, IP66, for connecting corrugated pipes to HEAVYCON EVO plastic cable glands or ADVANCE plastic housings.

RoHS

Key Commercial Data

Packing unit	10 pc
GTIN	 4 046356 860857
GTIN	4046356860857

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP66

General

Color	black
Type	With strain relief
	Internal thread
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V2
Material	PA
Assembly instructions	The corrugated pipe adapter is used in the screw connection instead of the union nut. Thanks to the adapter, corrugated pipes can be used.

Standards and Regulations

Halogen-free	yes
Flammability rating according to UL 94	V2

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---

Corrugated tube screw connection - WP-GR HF CTA M40 BK - 3241223

Technical data

Environmental Product Compliance

	No hazardous substances above threshold values
--	--

Classifications

eCl@ss

eCl@ss 10.0.1	27430308
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27140900
eCl@ss 5.1	27140900
eCl@ss 6.0	27140900
eCl@ss 7.0	27439201
eCl@ss 8.0	27439201
eCl@ss 9.0	27430308

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001469
ETIM 5.0	EC001469
ETIM 6.0	EC000441
ETIM 7.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

Accessories

Accessories

Corrugated pipe

Corrugated tube screw connection - WP-GR HF CTA M40 BK - 3241223

Accessories

Protective hose - WP-PA HF-SL 42,5 BK - 3240848



Polyamide protective hose, inflammability class V0, UV resistant

Protective hose - WP-PA HF 42,5 BK - 3241089



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 25 m

Protective hose - WP-PA HF-HB 42,5 BK - 3240844



Polyamide protective hose, inflammability class HB, UV resistant

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3241223