

Ink ribbon - THERMOMARK-RIBBON 110-WMS - 5145397

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ribbon sheet, length: 300 m, width: 110 mm, printing color: Black (specially for shrinking sleeves)

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 108034
GTIN	4046356108034

Technical data

Dimensions

Length (b)	300 m
Width (a)	110 mm

Ambient conditions

Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
--------------------------------	---

General

Color	black
Material	Polyester

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	19140611
eCl@ss 4.0	24190100
eCl@ss 4.1	24190100
eCl@ss 5.0	19029100
eCl@ss 5.1	19029100

Ink ribbon - THERMOMARK-RIBBON 110-WMS - 5145397

Classifications

eCl@ss

eCl@ss 6.0	19149200
eCl@ss 7.0	19149290
eCl@ss 8.0	19140611
eCl@ss 9.0	19140611

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001675
ETIM 5.0	EC001675
ETIM 6.0	EC001694
ETIM 7.0	EC001694

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43211612
UNSPSC 18.0	44103112
UNSPSC 19.0	44103112
UNSPSC 20.0	44103112
UNSPSC 21.0	44103112

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[5145397](#)