

## Snap-in markers - UCT-EM (10X5) CUS - 0801554

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

UniCard sheet, for labeling devices from other manufacturers, for overview table see download area, labeled according to customer specifications



### Key commercial data

|                      |                                                                                                        |
|----------------------|--------------------------------------------------------------------------------------------------------|
| Packing unit         | 1                                                                                                      |
| GTIN                 | <br>4 046356 682978 |
| Custom tariff number | 39269097                                                                                               |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 10 mm |
| Width (a)  | 5 mm  |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

#### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Color                                   | white                          |
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | V0                             |
| Material                                | PC                             |
| Wipe resistance                         | DIN EN 61010-1 (VDE 0411-1)    |
| Number of individual labels             | 60                             |
| Number of individual labels per row     | 10                             |
| RoHS compliant                          | Yes                            |
| Printability                            | Thermal transfer               |

## Snap-in markers - UCT-EM (10X5) CUS - 0801554

### Technical data

#### General

|                                                                     |                                    |
|---------------------------------------------------------------------|------------------------------------|
|                                                                     | Inkjet printing                    |
| Device                                                              | 5146464 THERMOMARK CARD            |
|                                                                     | 0830400 THERMOMARK CARD-UCT-MAG13  |
|                                                                     | 5147888 BLUEMARK LED               |
|                                                                     | 5147999 BLUEMARK CLED              |
| Ink ribbon                                                          | 0801371 THERMOMARK-RIBBON 110-TC   |
|                                                                     | 5147421 BLUEMARK FLUID-CARTRIDGE   |
|                                                                     | 5146662 BLUEMARK CLED-FLUID-CARTR. |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02               |
| Result                                                              | Test passed                        |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03       |
| Test duration                                                       | 96 h                               |
| Wipe resistance test result                                         | Test passed                        |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02          |
| Test duration                                                       | 96 h                               |
| Salt spray testing result                                           | Test passed                        |
| Alternating condensation climate with SO2 test specification        | DIN 50018:2013-05                  |
| Climate level                                                       | AHT 1.0 S                          |
| Cycles                                                              | 2                                  |
| Condensation test result                                            | Test passed                        |
| Wipe resistance of test specification inscriptions                  | IEC 61010-1:2010-06                |
| Result                                                              | Test passed                        |
| Marking mounting type                                               | snapped into marker carrier        |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
|----------|----------|

## Snap-in markers - UCT-EM (10X5) CUS - 0801554

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0801554