

## Sensor/actuator cable - SAC-5P-M12MS/10,0-802/M12FS - 1408370

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Sensor/actuator cable

RoHS

### Key Commercial Data

|                        |                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------|
| Packing unit           | 1 pc                                                                                                  |
| Minimum order quantity | 50 pc                                                                                                 |
| GTIN                   | <br>4 046356 804943 |
| GTIN                   | 4046356804943                                                                                         |

### Technical data

#### General

|               |         |
|---------------|---------|
| Rated voltage | 48 V AC |
|               | 60 V DC |

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Approvals

#### Approvals

#### Approvals

UL Listed / cUL Listed / cULus Listed

#### Ex Approvals

#### Approval details

## Sensor/actuator cable - SAC-5P-M12MS/10,0-802/M12FS - 1408370

### Approvals

|                    |                                                                                   |                                                                                                                                                       |               |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| UL Listed          |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 221474 |
|                    |                                                                                   |                                                                                                                                                       |               |
| Nominal voltage UN |                                                                                   | 125 V                                                                                                                                                 |               |
| Nominal current IN |                                                                                   | 4 A                                                                                                                                                   |               |

|                    |                                                                                   |                                                                                                                                                       |               |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| cUL Listed         |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 221474 |
|                    |                                                                                   |                                                                                                                                                       |               |
| Nominal voltage UN |                                                                                   | 125 V                                                                                                                                                 |               |
| Nominal current IN |                                                                                   | 4 A                                                                                                                                                   |               |

|              |                                                                                    |
|--------------|------------------------------------------------------------------------------------|
| cULus Listed |  |
|--------------|------------------------------------------------------------------------------------|

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1408370](#)