

Crimp contact - SACC-CC1,0-T-0,50-M AU PU100 - 1412351

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, contact diameter: 1 mm, turned, Pin, contact material: CuZn, contact surface: Ni/Au, connection cross section: 0.34 mm² ... 0.5 mm² AWG 22 ... 20

RoHS

Key Commercial Data

Packing unit	100 pc
GTIN	 4 046356 958097
GTIN	4046356958097

Technical data

Electrical characteristics

Rated current	4 A
---------------	-----

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

Mechanical characteristics

Conductor cross section	0.34 mm ² ... 0.5 mm ²
Connection cross section AWG	22 ... 20
Stripping length of the individual wire	8 mm
Contact diameter	1 mm
Insertion/withdrawal cycles	≥ 100

General

Type	Individual male contact
Connection method	Crimp connection
Contact type	turned

Material data

Contact material	CuZn
------------------	------

Crimp contact - SACC-CC1,0-T-0,50-M AU PU100 - 1412351

Technical data

Material data

Contact surface material	Ni/Au
--------------------------	-------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1412351