


| SPECIFICATIONS | | |
|-------------------------|---------------------|-------------|
| PARAMETERS | VALUES | UNITS |
| RATED VOLTAGE | 12 | Vac |
| OPERATING VOLTAGE RANGE | 4 ~ 28 | Vac/Vdc |
| RATED CURRENT (MAX) | 7 | mA |
| MINIMUM SPL @ 10 CM | 91 | dBA |
| RESONANT FREQUENCY | 2,800 ± 500 | Hz |
| TONE OR PULSE RATE | CONTINUOUS | 0 pulse/sec |
| OPERATING TEMPERATURE | -30 ~ +85 | °C |
| STORAGE TEMPERATURE | -40 ~ +95 | °C |
| HOUSING MATERIAL | ABS | - |
| TERMINAL MATERIAL | Sn PLATED BRONZE | - |
| WEIGHT | 33.8 | grams |

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.


©2003, Projects Unlimited Inc.

| REVISION HISTORY | | | |
|------------------|---|-----------|----------|
| LTR | DESCRIPTION | DATE | APPROVED |
| - | RELEASED FROM ENGINEERING | 6/7/2006 | |
| A | REVISED TO INVETOR 3-D DRAWING TEMPLATE | 3/10/2008 | B.R. |
| B | REVISED WEIGHT | 2/24/2020 | M.V. |



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

| | | | | | | | | |
|--|----------------|--|----------|------------|-----------------|--------------|----------------|------------|
| UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°. | SIZE A3 | Designed by | Date | Checked by | Date | Approved by | Date | Drawn Date |
| | | J.D. | 6/7/2006 | E.P. | 6/7/2006 | B.R. | 6/7/2006 | 3/10/2008 |
| | |  pui audio ™ inc | | | AI-4328-P-C28-R | | | |
| | Indicator | | | | | Edition - | Sheet 1 / 1 | |
| AI-4328-P-C28-R.idw | | | | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-4328-P-C28-R](#)