

SPECIFICATIONS


| PARAMETERS | VALUES | UNITS |
|---|-------------|-------|
| RATED INPUT POWER | 1.5 | W |
| MAX INPUT POWER | 3 | W |
| IMPEDANCE | 4 ± 15% | OHM |
| OUTPUT SPL @ 1W/1M (AT 1.0, 1.2, 1.5, 2.0 kHz) | 85 ± 3 | dBa |
| DISTORTION (MAX.) | 5% | - |
| RESONANT FREQUENCY | 800 ± 20% | Hz |
| FREQUENCY RANGE | 800 ~ 5,000 | Hz |
| HOUSING MATERIAL | METAL | - |
| CONE MATERIAL | PAPER | - |
| MAGNET MATERIAL | N35 | - |
| OPERATING TEMPERATURE | -25 ~ +65 | °C |
| WEIGHT | 15 | grams |

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.


REVISION HISTORY

| LTR | DESCRIPTION | DATE | APPROVED |
|-----|--|-----------|----------|
| - | RELEASED FROM ENGINEERING | 5/15/2006 | |
| A | REVISED TO INVENTOR 3-D DRAWING TEMPLATE | 1/6/2009 | B.R. |



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

| | | | | | | | | | | | |
|--|------|---|-----------|------------|---------------|-------------|-----------|------------|--|---------|-------|
| UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°. | SIZE | Designed by | Date | Checked by | Date | Approved by | Date | Drawn Date | | | |
| | | J.D. | 5/15/2006 | E.P. | 5/18/2006 | B.R. | 5/18/2006 | 1/6/2009 | | | |
| | A3 |  pui audio ™ inc <small>a projects unlimited company</small> | | | AS05004PR-2-R | | | | | | |
| | | | | | Speaker | | | | | Edition | Sheet |
| | | | | | | | | | | - | 1 / 1 |
| AS05004PR-2-R.idw | | | | | | | | | | | |



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS05004PR-2-R](#)