


## AS07708PS-2-R 77mm Speaker

3541 Stop Eight Road • Dayton, Ohio 45414

#### **Product Overview**


- 77mm speaker with square frame and 90 dB sensitivity
- ullet 4W continuous, 8W maximum power handling and 8 $\Omega$  impedance
- Paper cone for natural sound











# AS07708PS-2-R 77mm Speaker


Mechanical and Environment Testing					
Test Description	Test Condition				
High Temperature	85°C (±2°C) with random humidity for 48 hours				
Low Temperature	-40°C (±2°C) with random humidity for 48 hours				
Humidity	40°C (±2°C) with 90% to 95% relative humidity for 48 hours				
Power Test	White noise @ 4W input power for 48 hours				
Buzz and Rattle Test	5.66V sine wave				
After tests, speaker shall rest for 1 hour. SPL shall not deviate ±3 dB from pre-test measurement.					
Temperature Cycle Test	-10°C to 40°C, 4 cycles (refer to Temperature Cycle Test Graph)				
After test, speaker shall rest for 1 hour. SPL shall not deviate ±3 dB from pre-test measurement.					


SPECIFICATIONS						
PARAMETERS	VALUES	UNITS				
RATED INPUT POWER	4	W				
MAX INPUT POWER	8	W				
IMPEDANCE	8 ± 15%	OHM				
OUTPUT SPL @ 1W/0.5M	90 ± 3	dBA				
(AT 0.4, 0.5, 0.6, 0.8 kHz)	90±3	UDA				
DISTORTION (MAX.)	5%	-				
RESONANT FREQUENCY	250 ± 20%	Hz				
FREQUENCY RANGE	250 ~ 10,000	Hz				
HOUSING MATERIAL	METAL	-				
CONE MATERIAL	PAPER	-				
MAGNET MATERIAL	FERRITE	-				
OPERATING TEMPERATURE	-40 ~ +85	°C				
WEIGHT	118	grams				

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

REVISION HISTORY							
LTR	DESCRIPTION	DATE	APPROVED				
-	RELEASED FROM ENGINEERING	3/30/2006					
Α	ADDED MOUNTING HOLE DIMENSION	12/19/2007	R.W.				
В	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	1/28/2009	B.R.				
С	REVISED SEVERAL DIMENSIONS AND SPECIFICATIONS	1/24/2011	B.R.				
D	REVISED HOLE TO HOLE DIMENSION AND ROHS STATUS	7/16/2013	M.L.				
Е	REVISED OPERATING TEMPERATURE	9/16/2013	M.L.				







1/1

#### NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

UNLESS OTHERWISE		Designed by	Date	Date Checked b		Date	Approved by	Date	[	Drawn Date
SPECIFIED: DIMENSIONS ARE IN	SIZE	B.R.	3/30/2006	Е	3.R.	3/30/2006	E.P.	3/30/20	06 1	/28/2009
MILLIMETERS,		(X)		AC07700DC 2 D						
TOLERANCES ARE ±0.5 AND	A3 DUI.		A307700P3-Z-R							
ANGLES ARE ±3°.				тм			. 1		Edition	Sheet

Speaker AS07708PS-2-R.idw

### **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

PUI Audio: