
SPECIFICATIONS				
PARAMETERS	VALUES	UNITS		
RATED VOLTAGE	24	Vdc		
OPERATING VOLTAGE RANGE	18 ~ 28	Vdc		
TONE OUTPUT	SEE 32 TONE CHART	-		
CURRENT CONSUMPTION	SEE 32	mA - -		
(NOMINAL)	TONE CHART			
INGRESS PROTECTION	IP54 <u>∕</u> A			
LENS COLOR	AMBER			
FLASH RATE	1	PER/SECOND		
CASE MATERIAL/COLOR	ABS/RED	- - °C grams		
TERMINAL	SCREW			
OPERATING TEMPERATURE	-10 ~ +55			
WEIGHT	300			
·				

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

REVISION HISTORY				
LTR	DESCRIPTION	DATE	APPROVED	
-	RELEASED FROM ENGINEERING	12/16/2005		
Α	ADDED RoHS & BASE NOTES	5/21/2007	R.W.	
В	REVISED DETAIL "A" DIL SWITCH	3/12/2009	B.R.	
С	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	5/17/2010	B.R.	







DETAIL "A"

DETAIL "B"
VOLUME CONTROL



OPTIONAL BASES DEEP BASE: AWA-DBR U BASE: AWA-UBR

120Vac BASE: AWA-DBR-120

NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2002/95/EC COMPLIANT.
- 4. IP65 WITH USE OF AWA-DBR, AWA-DBR-120, OR AWA-UBR BASE.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS,
TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.

AVW-15SBR-AL-24.idw

•

J.A.F. 12/16/2005 E.P.

PUI

audio nc
a projects unlimited company

Date

Designed by

 Checked by
 Date
 Approved by
 Date
 Drawn Date

 E.P.
 12/16/2005
 B.R.
 12/16/2005
 5/17/2010

 AVW-15SBR-AL-24

Siren Edition Sheet 1/1

卆

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

PUI Audio:

AVW-15SBR-AL-24