




Data Sheet

SMT-0540-T-10-R


Specifications

Parameters	Values	Units
Rated Voltage	3	V
Operating Voltage Range	2 ~ 4	V
Current Draw at Rated Voltage	45	mA
Coil Resistance	35 ± 4.5	Ohms
Minimum SPL @ 10cm	78	dBA
Resonant Frequency	4,000	Hz
Weight	0.16	Grams
Environmental Compliances	RoHS/REACH	-
Storage Temperature	-40 ~ 85	°C
Operating Temperature	-30 ~ 70	°C


Measurement Method (Temp: 5 ~ 35 °C; Humidity: 45 ~ 85%; Atmosphere: 860 ~ 1060hPa)





Typical Frequency Response



Recommended Land Pattern




Reliability Testing

Type of Test	Test Specifications
High Temperature Test	96 hours at 85°C
Low Temperature Test	96 hours at -40°C
Humidity Test	12 hours at 60°C with relative humidity at 95%
Temperature Cycle Testing	<p>Run the test for 5 cycles, with each cycle consisting of:</p>  <p>1 cycle : 90 min</p>
Vibration Test	 <p>Make this test for the directions of X, Y and Z. for 2 hours each (total 6 hours).</p>
Drop Test	Fix transducer on PCB with polyester film (t=0.2mm, gross weight: 100g) and the height of 120cm on each of the six surfaces 3 times each.

After reliability test, let rest for 2 hours.


Dimensions




Tolerance: $\pm 0.2\text{mm}$

Packaging

2,000 PCS per 1roll by using the tapping M/C.



2rolls or 5rolls per 1 double(thick) carton box packed by polypropylene tape.



Specifications Revisions		
Revision	Description	Date
A	Released from Engineering	7/22/2022

- Note:
- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are $\pm 0.5\text{mm}$ and angles are $\pm 3^\circ$.
 - 2. Specifications subject to change or withdrawal without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMT-0540-T-10-R](#)