




THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

| PARAMETERS | VALUES | UNITS |
|-----------------------------|----------------|-------|
| RATED VOLTAGE (SQUARE WAVE) | 12 | Vp-p |
| OPERATING VOLTAGE RANGE | 3 ~ 18 | Vp-p |
| RATED CURRENT (MAX) | 8 | mA |
| CAPACITANCE | 11,000±30% | pF |
| MINIMUM SPL @ 10 CM | 90 | dBA |
| RESONANT FREQUENCY | 3,600±500 | Hz |
| OPERATING TEMPERATURE | -20 ~ +60 | °C |
| STORAGE TEMPERATURE | -30 ~ +70 | °C |
| HOUSING MATERIAL | ABS | - |
| TERMINAL MATERIAL | TIN-PLATED PBW | - |
| WEIGHT | 3.8 | grams |

REVISIONS


| LTR | DESCRIPTION | DATE | APPROVED |
|-----|---------------------------|---------|----------|
| - | RELEASED FROM ENGINEERING | 4/16/02 | |
| A | REVISED TO NEW TEMPLATE | 6/15/04 | R. W. |
| B | ADDED NOTE 3 | 4/29/05 | R. W. |



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. PART WASHABLE USING DEIONIZED WATER, OR PURE ISOPROPYL ALCOHOL.

FILE NAME
AT-24.DWG

| | | | |
|---|--|---|--|
| UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°. | |  projects® unlimited Dayton, Ohio | |
| APPROVALS | | DATE | |
| DRAWN <i>RABL</i> | | 4/02 | |
| APPROVED <i>S.J.</i> | | 4/02 | |
| DO NOT SCALE DRAWING | | SCALE: N.T.S. | |
| SIZE A | | DRAWING NO. AT-24 | |
| SHEET 1 OF 1 | | SHEET 1 OF 1 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-24](#)