





REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
1		DRAWING MODIFY	JAMY 4/18/06	
2		DRAWING MODIFY	Yuan 08/01/06	



NOTES:

ELECTRICAL:

- VOLTAGE RATING : 125 VAC RMS.
- CURRENT RATING : 1.5 AMP.
- CONTACT RESISTANCE : 35 MILLIOHMS MAX.
- INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
- DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

- HOUSING MATERIAL : NYLON+G.F.30% UL94V-0.COLOR YELLOW
- CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46$ mm.
- PLATING : GOLD PLATING OVER NICKEL.
- OPERATING LIFE : 750 CYCLES MIN.
- PCB RETENTION PRE-SOLDER : 1 LB MIN.
- PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:


- STORAGE : -40°C TO +85°C.
- OPERATION: -40°C TO +85°C.
- WAVE SOLDERING TEMPERATURE: 255°C TO 265°C (5~10 SECONDS).

4. RoHS COMPLIANT

MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

ROHS PART NUMBER: E5908-00CL8X-L

2- 6u" 5-50u"
3-15u" 4-30u"



PC Board Layout Component Side Shown

MM (INCH) TOLERANCES EXCEPT AS NOTED MM ± .0 ± 0.2 .00 ± 0.15 .000 ± 0.075 ANGLES ± 0.5 THIRD ANGLE PROJECTION		DFTO JAMY CHKD ANKUE MFO APPV LUSHENG MATERIAL : QT'Y : FINISH : SCALE : 1.5:1	DATE 10/17/05 DATE 2006/8/3 DATE DATE 2006/8/3	Pulse A TECHNICAL COMPANY RoHS Compliant FULL RISE ELECTRONIC CO., LTD TITLE 20.57 PCB JACK 8P DRAWING NO. GE593266-LA /PART NO. SEE NOTE DO NOT SCALE DRAWING	SIZE A3 REV 2 SHEET X OF Y
--	--	--	--	--	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5908-00CL82-L](#)