




REVISION RECORD		
REV	DESCRIPTION	DRFT
11	EXTEND MIDDLE METAL SPACER (DIM0.15) CONTROL METAL SPACER POSITION (DIM1.5)	Royzuo 6/06/13



- NOTES:
- MATERIAL:
CONNECTOR
HOUSING: GLASS FILLED LCP, UL94 V-0, BLACK
TERMINALS: PHOS-BRONZE t=0.2mm .
OVERMOLDED TERMINALS HOUSING: GLASS FILLED LCP, UL94 V-0, BLACK
CAGE ASSEMBLY: COPPER-NICKEL-ZINC ALLOY t=0.25mm.
LIGHT PIPES: POLYCARBONITE UL94V-0, CLEAR.
 - FINISH:
TERMINAL:
1)50u" MIN NICKEL PLATING OVER ALL.
2)COMPLIANT TAIL: 50u" TIN OVER 50u" MIN NICKEL.
3)30u" MIN GOLD PLATING ON MATING AREA.
 - PRESS FIT HOLES:
CONTACT:
1)HOLE DIAMETER AFTER PLATING: 0.41-0.51mm.
2)DRILLED HOLE: 0.535-0.585mm
CAGE:
1)HOLE DIAMETER AFTER PLATING: 1.00-1.10mm.
2)DRILLED HOLE: 1.125-1.175mm.
 - RATING:
1)VOLTAGE: 120V r.m.s
2)CURRENT RATING: 0.5Amp. MAXIMUM PER INDIVIDUAL CONTACT.
3)OPERATING TEMPERATURE: -55°C TO 85°C
4)INSULATION RESISTANCE: 1000 mega-ohms Min.

Qty Per:	TRAY	CARTON
	3	18

DETACHED LISTS	MM (INCH)		RoHS Compliant		 Pulse Electronics			
	TOLERANCES EXCEPT AS NOTED		TITLE					
	MM		METAL GASKET					
	.0 ± 0.25	±	SFP PLUS 2 BY 4 CAGE+CONNECTOR_P					
	.00 ± 0.20	±						
	.000 ± 0.10	±						
	ANGLES ± 1°		DFTO :	JACK	DRAWING NO. CSFPP014-L		SIZE	REV
			DATE :	10/15/10	/PART NO. SFPP014-L		A3	11
	THIRD ANGLE PROJECTION		SCALE : 1:1		DO NOT SCALE DRAWING		SHEET	1 OF 4

8

7

6

5


4

3


2

1

REVISION RECORD		
REV	DESCRIPTION	DRFT
11	EXTEND MIDDLE METAL SPACER (DIM0.15) CONTROL METAL SPACER POSITION (DIM1.5)	Royzuo 6/05/13'





BEZEL CUT-OUT CENTER SPACING DETAIL
BEZEL THICKNESS:0.8-2.6



DETACHED LISTS	MM (INCH)		RoHS Compliant		 Pulse Electronics		
	TOLERANCES EXCEPT AS NOTED		TITLE				
	MM		METAL GASKET				
	.0 ± 0.25	±	SFP PLUS 2 BY 4 CAGE+CONNECTOR_P				
	.00 ± 0.20	±					
	.000 ± 0.10	±					
	ANGLES ± 1°		DFTO : JACK	DRAWING NO. CSFPP014-L		SIZE	REV
	 THIRD ANGLE PROJECTION		DATE : 10/15/10	/PART NO. SFPP014-L		A3	11
			SCALE : 1:1	DO NOT SCALE DRAWING		SHEET	2 OF 4

REVISION RECORD		
REV	DESCRIPTION	DRFT
11	EXTEND MIDDLE METAL SPACER (DIM0.15) CONTROL METAL SPACER POSITION (DIM1.5)	Royzuo 6/05/13'



DETACHED LISTS	MM (INCH)		RoHS Compliant		 Pulse Electronics		
	TOLERANCES EXCEPT AS NOTED		TITLE				
	MM		METAL GASKET				
	.0 ± 0.25	±	SFP PLUS 2 BY 4 CAGE+CONNECTOR_P				
	.00 ± 0.20	±					
	.000 ± 0.10	±					
	ANGLES ± 1°		DFTO :	JACK	DRAWING NO. CSFPP014-L		SIZE
 THIRD ANGLE PROJECTION		DATE :	10/15/10	/PART NO. SFPP014-L		A3	11
		SCALE :	1:1	DO NOT SCALE DRAWING		SHEET	3 OF 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

SFPP014-L