


REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
△		DRAWING MODIFY	SKYCHEN 11/27/06'	

**NOTES:****ELECTRICAL:**

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : PBT+GF30% UL94V-0. COLOR:BLACK
2. CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
3. PLATING : GOLD PLATING OVER NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
2. OPERATION: -40°C TO +85°C.
- △3. WAVE SOLDERING TEMPERATURE: 230°C TO 250°C 3~5 SECONDS.
4. RoHS COMPLIANT.

MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

RoHS PART NUMBER: E5288-32G14X-L

1- 3u" 2- 6u"
3-15u" 4-30u"
5-50u"

DETACHED LISTS	MM (INCH)	DFTO SKYCHEN	DATE 07/01/06'
	TOLERANCES EXCEPT AS NOTED	CHKD ASHELLY	DATE 2006/11/27
	MM	MFO	DATE
	.0 ± 0.2 .00 ± 0.15 .000 ± 0.075	APPVL ANKUE	DATE 2006/11/27
ANGLES ± 0.5	± ± ±	MATERIAL :	
THIRD ANGLE PROJECTION	QT'Y :	FINISH :	
	SCALE : 5:4	DO NOT SCALE DRAWING	



RoHS Compliant

FULL RISE ELECTRONIC CO., LTD

**TITLE TOP ENTRY GANG JACK
(8 PORTS)**

DRAWING NO. GE523A30-LC

/PART NO. SEE NOTE

SIZE
A3

REV
1

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5288-32G145-L](#) [E5288-32G142-L](#)