


Toroidal Inductors

High Inductance



- High Frequency, low loss operation (up to 100 kHz)
- Encapsulated construction
- Ambient temperature range of -55C to +70C
- Good inductance stability with temperature

Electrical Specifications @ 25°C

Reference Operating Values					Design Control Values		
Part Number	Inductance Typical (mH)	IDC (AMPS)	Maximum ET_{OP} (V- μ Sec)	Energy Storage (μ J MIN) ¹	Inductance No DC (mH) ($\pm 20\%$) ²	DCR (Ω MAX)	Size Code
PE-50500NL	0.5	.60	110	90	.72	0.35	7
PE-50501NL	1.0	.35	160	60	1.51	0.75	7
PE-50502NL	2.0	.25	225	60	2.88	1.30	7
PE-50503NL	0.5	1.75	325	765	.72	0.35	8
PE-50506NL	0.5	2.75	650	1890	.75	0.25	9
PE-50508NL	2.0	1.50	1200	2250	2.70	0.75	9




Notes: 1. $\frac{LI^2}{2}$ ratings is the ability of the inductor to store energy.

2. Inductance measured at 0.4 Volts and 20 kHz.

Mechanical

Schematic

PE-XXXX




Size Code	A	B	C	D	E
7	.754 19,15	.400 10,16	.500 12,70	.625 15,87	0.03 0,76
8	1.140 28,95	.665 16,89	.500 12,70	1.00 25,40	0.03 0,76
9	1.416 35,96	.850 21,59	.500 12,70	1.250 31,75	0.03 0,76

Dimensions: $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

Inductance Variation with IDC Change



For More Information

Pulse Worldwide Headquarters

12220 World Trade Drive
San Diego, CA 92128
U.S.A.

Tel: 858 674 8100
Fax: 858 674 8262

Pulse Europe

Einsteinstrasse 1
D-71083 Herrenberg
Germany

Tel: 49 7032 78060
Fax: 49 7032 7806 135

Pulse China Headquarters

B402, Shenzhen Academy of
Aerospace Technology Bldg.
10th Kejinan Road
High-Tech Zone
Nanshan District
Shenzhen, PR China 518057
Tel: 86 755 33966678
Fax: 86 755 33966700

Pulse North China

Room 2704/2705
Super Ocean Finance Ctr.
2067 Yan An Road West
Shanghai 200336
China

Tel: 86 21 62787060
Fax: 86 2162786973

Pulse South Asia

135 Joo Seng Road
#03-02
PM Industrial Bldg.
Singapore 368363

Tel: 65 6287 8998
Fax: 65 6287 8998

Pulse North Asia

3F, No. 198
Zhongyuan Road
Zhongli City
Taoyuan County 320
Taiwan R. O. C.

Tel: 886 3 4356768
Fax: 886 3 4356823 (Pulse)
Fax: 886 3 4356820 (FRE)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2015. Pulse Electronics, Inc. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[PE-50503NL](#) [PE-50501NL](#) [PE-50502NL](#)