



A1RFRD10

REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD

**NOTES:****ELECTRICAL:**

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.
6. OPERATING: 750 CYCLES MIN.


MECHANICAL:

1. HOUSING MATERIAL : PBT+30%G.F UL94V-0. COLOR-BLACK.
2. INSERT MATERIAL : PBT+30%GF UL94V-0. COLOR-BLACK.
3. CONTACT MATERIAL : PHOSPHOR BRONZE 0.35mm THICKNESS.
4. PLATING : GOLD PLATING OVER NICKEL.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
 2. OPERATION: 0°C TO 70°C.
 3. WAVE SOLDERING TEMPERATURE: 230~250° (3~5 SECONDS)
- MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

PART NUMBER: E 5J 8 8 - 0 0 L 0 X X-L

TYPE: _____
G-STAMPED PIN
H-ROUND PINPLATING: 1-3u"
2-6u"
3-15u"
4-30u"
5-50u"

PC Board Thickness=1.60mm

PC Board Layout Component Side Shown

DETACHED LISTS	MM (INCH)	DFTO Jake	DATE 05/10/05	FULL RISE ELECTRONIC CO., LTD	
	TOLERANCES EXCEPT AS NOTED	CHKD SAMMY	DATE 2005/5/10		
	MM	MFO	DATE		
	.0 ± 0.20	APPLV LUSHENG	DATE 2005/5/10		
	.00 ± 0.15				
ANGLES ±	±	MATERIAL :		TITLE	
THIRD ANGLE PROJECTION		QT'Y :		LED JACK UTP W/O LED	
		FINISH :		DRAWING NO. GE5J3A16_LC	SIZE REV
		SCALE : 4:1		/PART NO. SEE NOTE	A3 0
				DO NOT SCALE DRAWING	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5J88-00LOG2-L](#)