


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.



REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	Updated Specifications	01-25-11	LY



WIRING:568B

P1	COLOR	P2
1	white/orange	1
2	orange	2
3	white/green	3
6	green	6
4	blue	4
5	white/blue	5
7	white/brown	7
8	brown	8

NOTE: ∞ TWISTED PAIR



CONTROLLED

- NOTES:
- CABLE: CAT.6 UTP
26AWG COPPER STRANDED WIRE. 4 TWISTED PAIRS, 30V,60°C
OUTER JACKET: COLOR: YELLOW, O.D.: 6.0 ± 0.2mm
JACKET MATERIAL: PVC
 - PLUG TYPE: MODULAR U.S. 8P8C GOLD PLATING 50u"
MATERIAL: PC UL 94V-2
S.R.: PVC 75P MOLD, COLOR: YELLOW
 - PACKING: 1PC/POLYBAG
 - RoHS COMPLIANT

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. WCI DIVISION		
		Part Number:	1226014-10	RoHS Compliant
0-1	0.15	Description: CAT.6 UTP 8P8C - 8P8C		
1-6	0.20			
6-18	0.30	UNIT: mm	REV.B	Approved / Date
18-50	0.50			
50-120	0.70	Drawn / Date	Checked / Date	Approved / Date
120-250	0.90	R.Nuti 09-16-10	09-16-10	LY / 09-16-10
250-500	1.20			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qualtek:](#)

[1226014-10](#)