


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	Updated Pin Out, Notes and Graphics	10-26-16	LY



NOTES:

- CABLE: UL20276
(28AWG*1PR+EAM)*4+(28AWG*1C+SAM)*3+
28AWG*1PR+28AWG*5C+AEB(AL) 65%
OUTER JACKET: BLACK, OD: 8.5 ± 0.2mm
- CONNECTOR: DVI 18+5 MALE
INSULATOR: BLACK
PIN G/F
NICKEL PLATED SHELL
THUMB SCREW: 2.8*32.5mm #4-40UNC
- CONNECTOR: DVI 18+5 MALE
INSULATOR: BLACK
PIN G/F
NICKEL PLATED SHELL
THUMB SCREW: 2.8*32.5mm #4-40UNC
- PVC MOLDED: COLOR V398 45P BLACK
- ELECTRICAL TEST:
<1>.100% OPEN SHORT & MISS WIRE TEST
<2>.INSULATION RESISTANCE: DC400V 10M ohm MIN.
<3>.CONDUCTOR RESISTANCE: 3 ohm MAX.
- PACKING: 1PC/POLYBAG

PIN OUT

CN1	CN2	CN1	CN2
1 WHITE	1	17 WHITE	17
2 BROWN	2	18 GREEN	18
3 DRAIN	3	19 DRAIN	19
6 YELLOW	6	23 WHITE	23
7 ORANGE	7	24 BLUE	24
8 BLACK	8	22 DRAIN	22
9 WHITE	9	C1 RED(CEN)	C1
10 RED	10	C2 GREEN(CEN)	C2
11 DRAIN	11	C3 BLUE(CEN)	C3
14 RED	14	C4 BLUE	C4
15 WHITE	15	C5 GREEN(S)+BLUE(S)+RED(S)	C5
16 VIOLET	16	SHELL BRAID& DRAIN SHELL	

CONTROLLED

Dim range (mm)		Qualtek Electronics Corp. WCI DIVISION		
Tolerance +/- (mm)		Part Number: 1321005-03 RoHS Compliant		
0-1	0.15	Description: DVI (18+5)P/M - DVI (18+5)P/M		
1-6	0.20			
6-18	0.30	UNIT: mm	REV.B	
18-50	0.50			
50-120	0.70	Drawn / Date	Checked / Date	Approved / Date
120-250	0.90	B.Grubb 01-11-07	01-11-07	JJH / 01-11-07
250-500	1.20			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

1321005-03