


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED



#### CONNECTION

CN1 CN2

1 ——— RED ——— 1

2 ——— WHITE ——— 2  
3 ——— GREEN ——— 3

4 ——— BLACK ——— 5

SHELL ——— BRAID&DRAIN ——— SHELL

#### NOTES:

- CABLE: UL2725  
28AWGx1PR+28AWGx2C+ AEB(AL) 65%  
OUTER JACKET: BLACK, OD: 4.0 ± 0.2mm
- CONNECTOR: USB 2.0 A TYPE FEMALE  
INSULATOR: WHITE PBT  
PIN G/F  
NICKEL PLATED SHELL
- CONNECTOR: MICRO USB 2.0 (B) 5P/M TYPE MALE  
INSULATOR: BLACK PBT  
PIN G/F  
NICKEL PLATED SHELL
- PVC MOLDED: COLOR 45P BLACK
- ELECTRICAL TEST:  
<1>.100% OPEN SHORT & MISS WIRE TEST  
<2>.INSULATION RESISTANCE: DC300V 10M ohm MIN.  
<3>.CONDUCTOR RESISTANCE: 2 ohm MAX.
- PACKING: 1PC/POLYBAG W/ LABEL

**CONTROLLED**

Dim range (mm)		Qualtek Electronics Corp. WCI DIVISION		
		Part Number:	3021069-01M	RoHS Compliant
0-1	0.15	Description: USB 4P(A)/F - MICRO USB 5P(B)/M		
1-6	0.20			
6-18	0.30	UNIT: mm	Drawn / Date	Checked / Date
18-50	0.50			
50-120	0.70	R. Nuti 09-25-17	09-25-17	Approved / Date LY / 09-25-17
120-250	0.90			
250-500	1.20			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

3021069-01M