


**Features:**



- Motor: Brushless DC
- Motor Protection: IC
- Bearing Type: Two Ball, Sleeve, or Hydro Dynamic
- Connection: UL 1007 AWG 24, 280mm Wire Leads
- Frame Material: Plastic UL94V-0
- Impeller Material: Plastic UL94V-0
- Operating Temp:
 - Two Ball: -10°C~70°C
 - Sleeve: -10°C~60°C
 - Hydro Dynamic: -10°C~70°C
- Life Expectancy:
 - Two Ball: 70,000 Hours
 - Sleeve: 30,000 Hours
 - Hydro Dynamic: 50,000 Hours

**Fan-S Division**

Model No.	Volt.	Current	Power	Rated Speed	Maximum AirFlow		Maximum Static Pressure		Noise Level	Weight
	(VDC)	(A)	(W)	(rpm)	(CMM)	(CFM)	(InAq)	(mmAq)	(dB/A)	(g)
FAD1-12032C * AW12	12	0.08	0.96	1450	1.682	59.461	0.075	1.905	26.9	213.0
FAD1-12032C * LW12	12	0.19	2.28	2000	2.348	82.891	0.123	3.124	36.2	213.0
FAD1-12032C * MW12	12	0.26	3.12	2400	2.803	99.069	0.167	4.241	41.1	213.0
FAD1-12032C * HW12	12	0.32	3.84	2750	3.161	111.710	0.241	6.121	43.3	213.0
FAD1-12032C * JW12	12	0.51	6.12	3200	3.776	133.440	0.317	8.051	48.4	213.0
FAD1-12032D * AW12	24	0.05	1.20	1450	1.682	59.461	0.075	1.905	26.9	213.0
FAD1-12032D * LW12	24	0.10	2.40	2000	2.348	82.981	0.123	3.124	36.2	213.0
FAD1-12032D * MW12	24	0.16	3.84	2400	2.803	99.069	0.167	4.241	41.1	213.0
FAD1-12032D * HW12	24	0.21	5.04	2750	3.161	111.710	0.241	6.121	43.3	213.0
FAD1-12032D * JW12	24	0.32	7.68	3200	3.776	133.440	0.317	8.051	48.4	213.0
FAD1-12032E * HW12	48	0.11	5.28	2750	3.161	111.710	0.241	6.121	43.3	213.0
FAD1-12032E * JW12	48	0.15	7.20	3200	3.776	133.440	0.317	8.051	48.4	213.0

* Indicates "B" (Ball Bearing), "S" (Sleeve), or "H" (Hydro Dynamic)

Noise is measured at the distance of one (1) meter from the axis of intake.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[FAD1-12032CBAW12](#) [FAD1-12032CBHW12](#) [FAD1-12032CBJW12](#) [FAD1-12032CBLW12](#) [FAD1-12032CBMW12](#)
[FAD1-12032CHAW12](#) [FAD1-12032CHHW12](#) [FAD1-12032CHJW12](#) [FAD1-12032CHLW12](#) [FAD1-12032CHMW12](#)
[FAD1-12032CSAW12](#) [FAD1-12032CSHW12](#) [FAD1-12032CSJW12](#) [FAD1-12032CSLW12](#) [FAD1-12032CSMW12](#)
[FAD1-12032DBAW12](#) [FAD1-12032DBHW12](#) [FAD1-12032DBLW12](#) [FAD1-12032DBMW12](#) [FAD1-12032DHAW12](#)
[FAD1-12032DHHW12](#) [FAD1-12032DHLW12](#) [FAD1-12032DHMW12](#) [FAD1-12032DSAW12](#) [FAD1-12032DSHW12](#)
[FAD1-12032DSLW12](#) [FAD1-12032DSMW12](#) [FAD1-12032EBHW12](#) [FAD1-12032EBJW12](#) [FAD1-12032EHHW12](#)
[FAD1-12032EHJW12](#) [FAD1-12032ESHW12](#) [FAD1-12032ESJW12](#)