

**Features:**



- Motor: Brushless DC
- Motor Protection: IC
- Bearing Type: Two Ball, Sleeve, or Hydro Dynamic
- Connection: UL 1007 AWG 24, 300mm Wire Leads
- Frame Material: Plastic UL94V-0
- Impeller Material: Plastic UL94V-0
- Operating Temp:
 - Two Ball: -10°C~70°C
 - Sleeve: -10°C~60°C
 - Hydro Dynamic: -10°C~70°C
- Life Expectancy:
 - Two Ball: 70,000 Hours
 - Sleeve: 30,000 Hours
 - Hydro Dynamic: 50,000 Hours

**Fan-S Division**

Model No.	Volt.	Current	Power	Rated Speed	Maximum AirFlow		Maximum Static Pressure		Noise Level	Weight
	(VDC)	(A)	(W)	(rpm)	(CMM)	(CFM)	(InAq)	(mmAq)	(dB/A)	(g)
FAD1-08015B * MW12	5	0.13	0.65	2440	0.617	21.805	0.078	1.981	24.9	62.0
FAD1-08015B * HW12	5	0.22	1.10	3200	0.841	29.722	0.122	3.098	34.4	62.0
FAD1-08015C * LW12	12	0.03	0.36	2000	0.518	18.335	0.052	1.320	18.8	62.0
FAD1-08015C * MW12	12	0.05	0.60	2440	0.617	21.805	0.078	1.981	24.9	62.0
FAD1-08015C * HW12	12	0.09	1.08	3200	0.841	29.722	0.122	3.098	34.4	62.0
FAD1-08015C * JW12	12	0.16	1.92	3800	0.971	34.338	0.173	4.394	38.1	62.0
FAD1-08015D * MW12	24	0.04	0.96	2440	0.617	21.805	0.078	1.981	24.9	62.0
FAD1-08015D * HW12	24	0.08	1.92	3200	0.841	29.722	0.122	3.098	34.4	62.0

* Indicates "B" (Ball Bearing), "S" (Sleeve), or "H" (Hydro Dynamic)

Noise is measured at the distance of one (1) meter from the axis of intake.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[FAD1-08015BBHW12](#) [FAD1-08015BBMW12](#) [FAD1-08015BHHW12](#) [FAD1-08015BHMW12](#) [FAD1-08015BSHW12](#)
[FAD1-08015BSMW12](#) [FAD1-08015CBHW12](#) [FAD1-08015CBJW12](#) [FAD1-08015CBLW12](#) [FAD1-08015CBMW12](#)
[FAD1-08015CHHW12](#) [FAD1-08015CHJW12](#) [FAD1-08015CHLW12](#) [FAD1-08015CHMW12](#) [FAD1-08015CSHW12](#)
[FAD1-08015CSJW12](#) [FAD1-08015CSLW12](#) [FAD1-08015CSMW12](#) [FAD1-08015DBHW12](#) [FAD1-08015DBMW12](#)
[FAD1-08015DHHW12](#) [FAD1-08015DHMW12](#) [FAD1-08015DSHW12](#) [FAD1-08015DSMW12](#)