



REV	CHANGE	DATE	DRN	CHK
	Drawn	02/27/17	SJ	T

TOLERANCE DETAILS					
1	D	+0.000 [ +0.00] -0.015 [-0.38]	6	SD	$\pm 0.005$ [ $\pm 0.13$ ]
2	L	$\pm 0.015$ [ $\pm 0.38$ ]	7	SL	$\pm 0.010$ [ $\pm 0.25$ ]
3	W	+0.000 [ +0.00] -0.010 [-0.25]	8	TL	$\pm 0.010$ [ $\pm 0.25$ ]
4	HD	$\pm 0.005$ [ $\pm 0.13$ ]	9	WL	+0.000 [ +0.00] -0.010 [-0.25]
5	HL	+0.000 [ +0.00] -0.015 [-0.38]			

#### NOTES:

1. Material : Stainless Steel
2. Finish :
3. ASME Y14.5-M - 2009
4. All Drawing Dimensions are in Inches [mm]
5. Unless otherwise specified; Edge Breaks, Radii or Countersinks 0.005-0.015



95 Silvermine Rd., Seymour CT 06483  
Tel: 203-888-2133, Fax: 203-888-9860

This Drawing is the Property of RAF.  
It contains confidential, proprietary  
information that is RAF property. Do  
not disclose to or duplicate for others  
except as authorized by RAF.

**TOLERANCES**  
ALL DIMENSIONS ARE INCHES  
(UNLESS OTHERWISE SPECIFIED)  
**METALLIC**  
LENGTHS < 6 INCHES  $\pm 0.005$   
LENGTH > 6 INCHES  $\pm 0.010$   
DIAMETERS:  $\pm 0.005$   
**NON-METALLIC**  
LENGTH:  $\pm 0.010$  DIAMETERS:  $\pm 0.010$   
**INTERNAL THREADS:**  
MINIMUM THREAD DEPTH

COMPONENT	PANEL SCREW
0841-SS  CAPTIVE PANEL SCREW STYLE 4	<b>SCALE</b>
	5.94
	<b>SHEET</b>
	1 of 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RAF Electronic Hardware:](#)

[0841-SS](#)