


**RECTRON****SEMICONDUCTOR**

TECHNICAL SPECIFICATION

See below
for
Part #

SOT-23 - Power Transistor and Darlington



Maximum Ratings Electrical Characteristics (at Ta = 25°C unless otherwise specified)

Part #	Polarity	V_{CBO} (V) Min	V_{CEO} (V) Min	V_{EBO} (V) Min	P_D (W) @ 25 °C	I_C (A)	I_{CBO} (μ A) @ V_{CB} Max	h_{FE} Min	h_{FE} @ I_C (A) Max	V_{CE} (V)	$V_{CE(SAT)}$ (V) Max	$V_{BE(SAT)}$ (V) min - max @ I_C (A)	f_T (MHz) Min	I_C (mA)
*BC807	PNP	50 ¹	45	5	0.25	0.5	100 20	100	600	100	1	0.70	500	10
*BC808	PNP	30 ¹	25	5	0.25	0.5	100 20	100	600	100	1	0.70	500	10
*BC817	NPN	50 ¹	45	5	0.25	0.5	100 20	100	600	100	1	0.70	500	10
*BC818	NPN	30 ¹	25	5	0.25	0.5	100 20	100	600	100	1	0.70	500	10
*BC846	NPN	80	65	6	0.25	0.1	15 30	110	450	2	5	0.60	100	10
*BC847	NPN	50	45	6	0.25	0.1	15 30	110	800	2	5	0.60	100	10
*BC848	NPN	30	30	5	0.25	0.1	15 30	110	800	2	5	0.60	100	10
*BC849	NPN	30	30	5	0.25	0.1	15 30	200	800	2	5	0.60	100	10
*BC850	NPN	50	45	5	0.25	0.1	15 30	200	800	2	5	0.60	100	10
*BC856	PNP	80	65	5	0.25	0.1	15 30	125	475	2	5	0.65	100	10
*BC857	PNP	50	45	5	0.25	0.1	15 30	125	800	2	5	0.65	100	10
*BC858	PNP	30	30	5	0.25	0.1	15 30	125	800	2	5	0.65	100	10
*BC859	PNP	30	30	5	0.25	0.1	15 30	125	800	2	5	0.65	100	10
*BC860	PNP	50	45	5	0.25	0.1	15 30	125	800	2	5	0.65	100	10
BF820	NPN	300	300 ²	5	0.25	0.05	10 200	50		25	20	0.60	30	10
BF821	PNP	300	300 ²	5	0.25	0.05	10 200	50		25	20	0.80	30	10
BF822	NPN	250	250	5	0.25	0.05	10 200	50		25	20	0.60	30	10
BF823	PNP	250	250	5	0.25	0.05	10 200	50		25	20	0.80	30	10
BF840	NPN	40	40	4	0.25	0.025	100 20	67	222	1	10		380	1
BF841	NPN	40	40	4	0.25	0.025	100 20	36	125	1	10		380	1

* h_{FE} ¹ V_{CES} ² V_{CER} ³ I_{CEX} ⁴MIN ⁵MAX

Part #	Polarity	V _{CBO} (V) Min	V _{CEO} (V) Min	V _{EBO} (V) Min	P _D (W)	I _C (A)	I _{CBO} (uA) Max	@ V _{CB} (V)	h _{FE} Min	h _{FE} @ Max	I _C (A)	V _{CE} (V)	V _{CE(SAT)} (V) Max	V _{BE(SAT)} (V) Mn-Mx	@ I _C (mA)	f _T (MHz)	@ I _C (mA)
CMBT918	NPN	30	15	3	0.225	0.35	50	15	20		3	1	0.40	- 1.00 ⁴	10	-	4
CMBT2222A	NPN	75	40	6	0.25	0.6	10	60	100	300	150	10	0.30	0.60 ⁴ 1.20 ⁵	150	-	20
CMBT2907A	PNP	60	60	5	0.25	0.6	10	50	100	300	150	10	0.40	- 1.30 ⁵	150	-	50
CMBT3904	NPN	60	40	6	0.25	0.2	50 ³	30	100	300	10	1	0.20	0.65 ⁴ 0.85 ⁵	10	-	10
CMBT3906	PNP	40	40	5	0.25	0.2	50 ³	30	100	300	10	1	0.25	0.65 ⁴ 0.85 ⁵	10	-	10
CMBT4401	NPN	60	40	6	0.25	0.6	100 ³	35	100	300	150	1	0.40	0.75 ⁴ 0.95 ⁵	150	-	20
CMBT4403	PNP	40	40	5	0.25	0.6	100 ³	35	100	300	150	2	0.40	0.75 ⁴ 0.95 ⁵	150	-	20
CMBT5401	PNP	160	150	5	0.25	0.5	50	120	60	240	10	5	0.20	- 1.00 ⁵	10	300 ⁵	10
CMBT5551	NPN	180	160	6	0.25	0.6	50	120	80	250	10	5	0.15	- 1.00 ⁵	10	300 ⁵	10
CMBTA05	NPN	60	60	4	0.25	0.5	100	60	100	-	100	1	0.25	-	100	-	10
CMBTA06	NPN	80	80	4	0.25	0.5	100	80	100	-	100	1	0.25	-	100	-	10
CMBTA13	NPN	30	30 ¹	10	0.25	0.3	100	30	10k	-	100	5	1.50	-	100	-	10
CMBTA14	NPN	30	30 ¹	10	0.25	0.3	100	30	20k	-	100	5	1.50	- -	100	-	10
CMBTA42	NPN	300	300	6	0.25	0.5	100	200	40	-	10	10	0.50	- 0.90 ⁵	20	-	10
CMBTA55	PNP	60	60	4	0.25	0.5	100	60	100	-	100	1	0.25	-	100	-	100
CMBTA56	PNP	80	80	4	0.25	0.5	100	80	100	-	100	1	0.25	-	100	-	100
CMBTA92	PNP	300	300	5	0.25	0.5	250	200	40	-	10	10	0.50	- 0.90 ⁵	20	-	10
CMMT451	NPN	80	60	5	0.5	1.0	100	60	50	150	150	10	0.35	- 1.10 ⁵	150	-	50
CMMT491	NPN	80	60	5	0.5	1.0	100	60	100	300	500	5	0.25	-	500	-	50
CMMT551	PNP	80	60	5	0.5	1.0	100	60	50	150	150	10	0.35	- 1.10 ⁵	150	-	50
CMMT591	PNP	80	60	5	0.5	1.0	100	60	100	300	500	5	0.30	-	500	-	50
CSA1162GR	PNP	50	50	5	0.15	0.15	100	50	200	400	2	6	0.30	-	100	-	1
CSA1362GR	PNP	15	15	5	0.2	0.80	100	15	200	400	100	1	0.25	-	400	120 ⁴	10
CSC2712GR	NPN	60	50	5	0.15	0.15	100	60	200	400	2	6	0.25	-	100	-	1
CSD1306E	NPN	30	15	5	0.2	0.70	100- 0	20	400	800	150	1	0.50	-	500	250 ⁴	150

¹I_{CEO} ²I_{CBO} ³V_{CES} ⁴I_{CER} ⁵f_T Typical Values

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rectron:](#)

[BC807-T](#) [CMBTA56-T](#) [CMBT4403-T](#) [CMBTA06](#) [CMBT3906-T](#) [CMBT3906](#) [CMBTA56](#) [CMBTA42-T](#) [CMBT4401-T](#)
[CMBTA42](#) [CMBT3904](#) [CMBT4403](#) [CMBTA92](#) [CMBT5551](#) [CMBT5401](#) [CMBT5551-T](#) [CMBT3904-T](#) [CMBTA92-T](#)
[CMBTA06-T](#) [CMBT5401-T](#) [CMBT4401](#) [CMBT9014](#) [MMBT5551](#)