


Samples can deviate in the execution from the serie.



All dimensions in mm

Holder material : heat resistant, glass-fiber reinforced LCP

Battery contacts : spring stainless steel 301 nickel plated throughout

Solder contacts : spring stainless steel 301 solder area tin-plated throughout, min. thickness 5um

All framed values will be used for dimension checking !

The Products of Renata SA are neither designed nor authorized for use in certain areas of application of environment.

For further details we refer to our webpage [www.renata.com/downloads/restriction\\_of\\_use](http://www.renata.com/downloads/restriction_of_use)

Dimensions and tolerances can be specified only after the testing of the devices for the mass production definitely

Rev.	①	27.08.19	PWu	Rev.	○				Customer's Approval		
Rev.	○			Rev.	○				Date		
Rev.	○			Rev.	○				Signature		
Title:  SMTU2032-C								Scale 2:1	Drawn	17.04.12	Wu Ping
									Checked		
									Approved		
<b>renata</b> batteries CH-4452 Itingen Switzerland								10.0833.4-1			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Renata:

[SMTU2032-G.TR](#) [SMTU2032-G](#) [SMTU2032-C](#) [SMTU2032-C.TR](#)