



# Series 600 DIP Headers w/Coined Contacts

## FEATURES

- Aries offers a full line of DIP headers, available with either coined or screw machine contacts. Consult [Data Sheet 12035](#) for screw machine contacts.
- Snap-on, protective covers are available for all sizes shown below and accommodate 0.125 [3.18] to 0.750 [9.05] component heights. Consult [Data Sheet 12033](#) for snap-on protective covers.
- Body cavity design provides additional clearance for component mounting.

## GENERAL SPECIFICATIONS

- BODY MATERIAL:** Black UL 94V-0 Glass-filled 4/6 Nylon
- COINED CONTACTS:** Brass, 1/2-hard
- CONTACT PLATING:** "0" = 200μ [5.08μm] min. matte Sn plating per ASTM B545-97 over 50μ [1.27μ] min. Ni per QQ-N-290 -OR- "0TL" = 200u" [5.08μm] 90/10 Sn/Pb per MIL-T-10727 Type I over 50u" [1.27μm] min. Ni per QQ-N-290 -OR- "1" = 10u" [.25μm] Au per MIL-G-45204 over 50u" [1.27μm] min. Ni per QQ-N-290
- CONTACT CURRENT RATING:** 2 amps
- OPERATING TEMPERATURE:** -67°F to 221°F [-55°C to 105°C] for Sn and Sn/Pb plating; -67°F to 257°F [-55°C to 125°C] for Au plating
- FORK CONTACTS ACCEPTS LEADS:** up to 0.025 [0.64] diameter

## MOUNTING CONSIDERATIONS

- SUGGESTED PCB HOLE SIZE:** 0.035 ± 0.002 [0.89 ± 0.05] diameter



## ORDERING INFORMATION

**XX-600-X X**

### Plating

0 = Sn  
0TL = Sn/Pb  
1 = Au


### Pin Style

1 = Fork  
2 = Post


### Series

### No. of Pins

0.300 - 4 thru 20  
0.400 - 22  
0.600 - 24, 28, 40  
See Table below





**.300 [7.62] CENTERS BODY**  
(with numbered pin positions, no ribs)



**.400 [10.16] AND .600 [15.24] CENTERS BODY**  
(with ribs)

Centers "C"	Dim. "D"	Dim. "E"
0.300 [7.62]	0.395 [10.03]	0.252 [6.40]
0.400 [10.16]	0.495 [12.57]	0.352 [8.94]
0.600 [15.24]	0.695 [17.65]	0.552 [14.02]



ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: ±0.005 [0.13] UNLESS OTHERWISE SPECIFIED

"A" = (NO. OF PINS PER ROW x 0.100 [2.54]) + 0.050 [1.27]

"B" = (NO. OF PINS PER ROW - 1) x 0.100 [2.54]

FOR SCREW MACHINE CONTACTS, SEE [DATA SHEET 12036](#)

CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION. SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE CONSIDERED UNCONTROLLED



**ARIES**  
ELECTRONICS, INC.

2609 Bartram Road • Bristol, PA 19007-6810 USA  
TEL 215-781-9956 • FAX 215-781-9845  
[WWW.ARIESELEC.COM](http://WWW.ARIESELEC.COM) • [INFO@ARIESELEC.COM](mailto:INFO@ARIESELEC.COM)



12032  
Rev. 7.1  
1 of 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aries Electronics:](#)

[40-600-20](#) [1109241](#)