

8800 SERIES UNI-SEAL DROP TOOL

This universal drop tool is designed for use with environmentally sealed RG6 and RG59 male F compression connectors.

SARGENT QUALITY TOOLS



Made in U.S.A.

Uni-Seal Drop Tool Features:

- A universal tool for RG6 and RG59 male drop F compression connectors produced by Thomas & Betts, Gilbert, PPC, Antec/Digicon, PCT, Stirling and others.
- A toggle action to assure complete connector sealing, thus eliminating the need for a complicated ratchet mechanism.
- The tool incorporates high mechanical advantage to reduce compression force during connector installation. This ergonomic design minimizes user fatigue and promotes high levels of productivity.
- Cable positioners provide 360° connector support during compression. This design eliminates faulty compressions such as tight nuts, bent connectors or popped o-rings.
- Handle activation allows easy access when terminating in a M.D.U. enclosure or dealing with a short stub-in.
- The natural grasp of the tool allows the handle to open the actuation chamber for easy connector insertion.
- All metal parts are high carbon steel heat treated for longevity of operation.
- No exposed retaining rings to catch on objects causing the tool to dis-assemble.
- Handle grips are molded from Hytrel making the tool durable and highly visible.
- Tools conservatively rated for 25,000 cycles on high load connectors and easily field re-furbished.



Ordering Information:

Application		Uni-Seal Part Number
T & B Gilbert PPC Antec PCT	Snap-N-Seal™	8800 US
	Ultra Seal™	
	EXXL	
	Digicon™	
	DRS	
PPC	EX Series	8820 US
Stirling	SPL	8810 US

Specifications:

Weight	8 oz / 228.6 grams
Length	8 inches / 20.3 cm
Warranty	1 year

Accessories:

Cable Preparation	8720 ES
-------------------	---------

ROSTRA TOOL COMPANY
30 E. INDUSTRIAL RD.
BRANFORD, CT 06405 USA

PHONE: 203-488-8665
FAX: 203-488-6497
www.rostratool.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sargent Tools:

[8820US](#) [8800US](#) [8810US](#)