

## 6225XXASRS-DC3

Relay, SE Relays, solid state, SPST NC, 25A, 24...280 VAC, 3...32 VDC Uc, triac random switching, screw terminal



### Main

|                          |                   |
|--------------------------|-------------------|
| Range                    | Legacy            |
| Product Type             | Solid state relay |
| Maximum output current   | 25 A AC           |
| Mounting Support         | Panel             |
| Network Number of Phases | 1 phase           |
| Output Voltage           | 24...280 V AC     |
| Control Circuit Voltage  | 3...32 V DC       |

### Complementary

|                               |  |
|-------------------------------|--|
| Input Impedance               | 1.5 kOhm   |
| Holding Current               | 40 mA  |
| Input Current Limits          | 3.4...20 mA at 5 V DC  |
| Switch Function               | SPST   |
| Contacts Type and Composition | NC   |
| Protection Technology         | Current limiter  |
| Tightening Torque             | 10 lb.in for input<br>20 lb.in for output  |
| Connections Terminals         | Input screw clamp terminal, 1<br>Output screw clamp terminals, 1                                       |
| Screw Type                    | M3.5<br>M6   |
| Local Signalling              | For input status 1 LED (green)   |
| Switching Device              | SCR output<br>Random voltage switching   |
| Surge Current                 | 250 A 16.6 ms  |
| Must Release Voltage          | 1 V  |
| Power Factor                  | 1  |
| Insulating Resistance         | 1 GΩ   |
| Thermal Resistance            | 1.02 °C/W  |
| Maximum I²t for fusing        | 250 A².s   |
| Leakage Current               | 1 mA   |
| Response Time                 | 8.33 ms (turn-on)<br>8.33 ms (turn-off)  |
| Dielectric Strength           | 4000 V between input and ground<br>4000 V between output and ground<br>4000 V between input and output |
| Height                        | 1.39 in (35.3 mm)  |
| Width                         | 1.85 in (47.1 mm)  |
| Depth                         | 2.30 in (58.4 mm)  |
| Product Weight                | 3.70 oz (105 g)  |

## Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Product Certifications                | UL<br>CSA<br>CE             |
| IP Degree of Protection               | IP20                        |
| Ambient Air Temperature for Operation | -40...176 °F (-40...80 °C)  |
| Ambient Air Temperature for Storage   | -40...257 °F (-40...125 °C) |





## Ordering and shipping details

|                       |                  |
|-----------------------|------------------|
| GTIN                  | 3606480277337    |
| Nbr. of units in pkg. | 1                |
| Package weight(Lbs)   | 3.05 oz (86.5 g) |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Package 1 Height             | 2.28 in (5.791 cm)     |
| Package 1 width              | 1.71 in (4.342 cm)     |
| Package 1 Length             | 1.74 in (4.414 cm)     |
| Unit Type of Package 2       | BB1                    |
| Number of Units in Package 2 | 1                      |
| Package 2 Weight             | 3.05 oz (86.5 g)       |
| Package 2 Height             | 2.52 in (6.4 cm)       |
| Package 2 width              | 1.46 in (3.7 cm)       |
| Package 2 Length             | 1.85 in (4.7 cm)       |
| Unit Type of Package 3       | CAR                    |
| Number of Units in Package 3 | 50                     |
| Package 3 Weight             | 14.48 lb(US) (6.57 kg) |
| Package 3 Height             | 5.31 in (13.5 cm)      |
| Package 3 width              | 9.06 in (23 cm)        |
| Package 3 Length             | 10.63 in (27 cm)       |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           |  <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>  |
| Mercury free               | Yes   |
| RoHS exemption information |  <a href="#">Yes</a>   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |

Connections and Wiring Diagrams



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[6225XXASRS-DC3](#)