

6425AXXTZB-DC3

Relay, SE Relays, solid state, SPST NO, 25A, 48...530 VAC, 3...32 VDC Uc, triac AC zero cross, blade terminal



Main

Range	Legacy
Product Type	Solid state relay
Maximum output current	25 A AC
Mounting Support	Panel
Network Number of Phases	1 phase
Output Voltage	48...530 V AC
Control Circuit Voltage	3...32 V DC

Complementary

Holding Current	80 mA
Input Current Limits	16 mA DC typical
Switch Function	SPST
Contacts Type and Composition	NO
Tightening Torque	10 lb.in for input 20 lb.in for output
Connections Terminals	Input blade terminal 1 x 4.74 mm ² Output blade terminal 1 x 6.35 mm ²
Local Signalling	For input status 1 LED (green)
Switching Device	Triac output Zero voltage switching
Surge Current	250 A 16.6 ms
Must Release Voltage	1 V
Voltage Drop	<1.6 V on-state AC
Power Factor	With maximum load
Insulating Resistance	1 GΩ
Thermal Resistance	1.2 °C/W
Maximum I ² t for fusing	200 A ² .s 8.3 ms
Leakage Current	10 mA
DV/dt	250 V/μs off-state at maximum rated voltage
Response Time	0.5 cycle (turn-on) 0.5 cycle (turn-off)
Dielectric Strength	4000 V between input and ground 4000 V between output and ground 4000 V between input and output
Height	1.39 in (35.3 mm)
Width	1.85 in (47.1 mm)
Depth	2.30 in (58.4 mm)
Product Weight	3.05 oz (86.5 g)

Environment

Product Certifications	UL CSA CE
IP Degree of Protection	IP20
Ambient Air Temperature for Operation	-22...176 °F (-30...80 °C)
Ambient Air Temperature for Storage	-40...212 °F (-40...100 °C)





Ordering and shipping details

GTIN	3606480277474
Nbr. of units in pkg.	1
Package weight(Lbs)	3.05 oz (86.5 g)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.28 in (5.791 cm)
Package 1 width	1.71 in (4.342 cm)
Package 1 Length	1.74 in (4.414 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	1
Package 2 Weight	3.05 oz (86.5 g)
Package 2 Height	2.52 in (6.4 cm)
Package 2 width	1.46 in (3.7 cm)
Package 2 Length	1.85 in (4.7 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	14.48 lb(US) (6.57 kg)
Package 3 Height	5.31 in (13.5 cm)
Package 3 width	9.06 in (23 cm)
Package 3 Length	10.63 in (27 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Connections and Wiring Diagrams



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[6425AXXTZB-DC3](#)