



Main

Product Range	Legacy
Product Type	Signalling indicator
Product Compatibility	Socket 70-750 plug-in Socket 70-783 plug-in Socket 70-784 plug-in Socket 70-788 plug-in

Complementary

[Ue] rated operational voltage	24 V
Local Signalling	For coil powered 1 LED (green)
Width	1.37 in (34.80 mm)
Depth	1.59 in (40.5 mm)

Ordering and shipping details

GTIN	3606480278242
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14 oz (4.0 g)


Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.39 in (0.982 cm)
Package 1 width	1.37 in (3.47 cm)
Package 1 Length	0.06 in (0.16 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.41 oz (40.0 g)
Package 2 Height	0.04 in (0.1 cm)
Package 2 width	3.15 in (8 cm)
Package 2 Length	4.72 in (12 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	28.22 oz (800.0 g)
Package 3 Height	5.31 in (13.5 cm)
Package 3 width	6.69 in (17 cm)
Package 3 Length	10.43 in (26.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Connections and Wiring Diagrams



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[70-ASMLG-24](#)