

861HSSR210-DC-1

Relay, SE Relays, solid state, SPST NO, 10A, 24...280 VAC, 3...32 VDC, SCR, AC zero cross, hazardous locations approved



Main

Range	Legacy
Product Type	Solid state relay
Maximum output current	10 A AC
Mounting Support	Panel DIN rail
Network Number of Phases	1 phase
Output Voltage	24...280 V AC
Control Circuit Voltage	3...32 V DC

Complementary

Holding Current	50 mA
Input Current Limits	16 mA at 5 V DC typical
Switch Function	SPST
Contacts Type and Composition	NO
Protection Technology	Current limiter
Protection Type	Reverse polarity protection
Tightening Torque	0.8 N.m for input/output
Connections Terminals	Input/output screw clamp terminal 0.00 in ² (2.5 mm ²) AWG 14)
Local Signalling	For input status 1 LED (green)
Switching Device	SCR output Zero voltage switching
Load Current	10 A at nominal load 8 A incandescent lamp 4.5 A motor
Overload Current	24 A for 1 second
Surge Current	500 A 1 cycle
Must Release Voltage	1 V
Voltage Drop	<1.6 V peak AC <1.25 V on-state AC
Thermal Resistance	0.66 °C/W
Maximum I ² t for fusing	1250 A ² .s 8.3 ms
Leakage Current	6 mA at off-state 240 V AC
DV/dt	500 V/μs off-state at maximum rated voltage
Response Time	8.33 ms (turn-off) 8.33 ms (turn-on)
Dielectric Strength	4000 V between input and output 2500 V between terminals and chassis
Height	2.56 in (65 mm)
Width	0.62 in (15.75 mm)
Depth	3.54 in (89.93 mm)
Product Weight	4.48 oz (127.1 g)
Device Presentation	Complete device

Environment

Product Certifications	CE CSA UL
IP Degree of Protection	IP20
Ambient Air Temperature for Operation	-22...176 °F (-30...80 °C)
Ambient Air Temperature for Storage	-40...212 °F (-40...100 °C)

Ordering and shipping details

GTIN	3606480282140
Nbr. of units in pkg.	1
Package weight(Lbs)	4.48 oz (127.1 g)

Packing Units


Unit Type of Package 1	PCE
Package 1 Height	3.64 in (9.24 cm)
Package 1 width	0.69 in (1.76 cm)
Package 1 Length	2.56 in (6.5 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	1
Package 2 Weight	4.48 oz (127.1 g)
Package 2 Height	2.56 in (6.5 cm)
Package 2 width	0.63 in (1.6 cm)
Package 2 Length	3.94 in (10 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	10
Package 3 Weight	2.80 lb(US) (1.271 kg)
Package 3 Height	2.87 in (7.3 cm)
Package 3 width	4.21 in (10.7 cm)
Package 3 Length	7.72 in (19.6 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

[illegible]

Connections and Wiring Diagrams



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[861HSSR210-DC-1](#)