



Main

Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body Material	Zinc alloy
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Switch actuation	CW and CCW
Tilting angle	45 °
Torque Value	3 lbf.in (0.34 N.m)

Environment

Ambient air temperature for operation	-20...185 °F (-29...85 °C)
Product Certifications	CSA UL Listed CE

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901919926
Nbr. of units in pkg.	1
Package weight(Lbs)	20.00 oz (566.991 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.80 in (9.652 cm)
Package 1 width	5.80 in (14.732 cm)
Package 1 Length	8.70 in (22.098 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007C54CY1912](#)